

170 Series Digital Multimeters

Versatile meters for field service or bench repair

These meters have the features needed to find most electrical, electro-mechanical and heating and ventilation problems. They are simple to use and have significant improvements over Fluke's original 70 Series like, True-RMS, more measurement functions, conformance to the latest safety standards, and a much larger display that's easier to view.



Fluke 179



Fluke 177



Fluke 175



On all inputs

LISTED



Included Accessories

Test leads with 4 mm lantern tips and protective cap, installed 9V battery and users manual. The 179 also includes the 80BK temperature probe.

Ordering Information

Fluke 175 True RMS Multimeter
Fluke 177 True RMS Multimeter
Fluke 179 True RMS Multimeter
Fluke 179/EDA2 Kit Electronics Combo Kit
Fluke 179/MAG2 Kit Industrial Combo Kit

Features

	175	177	179
True-RMS measurements	AC	AC	AC
Digital display counts, updates 4 times per second	6000	6000	6000
Display backlight		•	•
Analog bargraph / segments, updates 40 times per second	33-segments	33-segments	33-segments
Auto and Manual ranging	•	•	•
Display Hold and AutoHOLD®	•	•	•
Min-Max-Average recording mode with Min/Max Alert	•	•	•
Temperature readings (bead thermocouple probe included)			•
Smoothing mode allows filtering of rapidly changing inputs	•	•	•
Audible continuity and diode test	•	•	•
Test lead alert	•	•	•
Unsafe voltage alert warns for voltages above 30V	•	•	•
Low battery indication	•	•	•
Ergonomic case with integrated holster	•	•	•
Easy battery and fuse exchange without opening the complete case	•	•	•
Selectable sleep mode preserves battery life	•	•	•

Specifications

(Check the Fluke web for detailed specifications)

Functions	Maximum	Max. resolution	175	177	179
Voltage DC	1000V	0.1mV	±(0.15%+2)	±(0.09%+2)	±(0.09%+2)
Voltage AC	1000V	0.1mV	±(1.0%+3)	±(1.0%+3)	±(1.0%+3)
Current DC	10A	0.01mA	±(1.0%+3)	±(1.0%+3)	±(1.0%+3)
Current AC	10A	0.01mA	±(1.5%+3)	±(1.5%+3)	±(1.5%+3)
Resistance	50MΩ	0.1Ω	±(0.9%+1)	±(0.9%+1)	±(0.9%+1)
Capacitance	10000µF	1nF	±(1.2%+2)	±(1.2%+2)	±(1.2%+2)
Frequency	100kHz	0.01Hz	±(0.1%+1)	±(0.1%+1)	±(0.1%+1)
Temperature	-40°C/+400°C	0.1°C			±(1.0%+10)

Accuracies are best accuracies for each function

Battery Life: Alkaline, 200 hrs typical
Size (HxWxD): 190 mm x 85 mm x 45 mm

Weight: 0.42 kg
Lifetime Warranty

Recommended Accessories



i400



C90



TLK-220



SV225



i410-i1010