

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0850010476

Status:

Obsolete

Description:

2.54mm (.100") Pitch DIN 41612 Header, Style B , Right Angle , Through Hole , 0.25µm (10µ") Selective Gold (Au) , 64 Circuits

Documents:

Drawing (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Backplane Connectors
Series	85001
Application	Daughtercard
Component Type	PCB Header
Product Name	IEC 603-2/DIN 41612
Style	B
Physical	
Circuits (Loaded)	64
Circuits (maximum)	64
Durability (mating cycles max)	50
Flammability	94V-0
Keying to Mating Part	None
Number of Columns	16
Number of Pairs	Open Pin Field
Number of Rows	2
Orientation	Right Angle
PC Tail Length	3.00mm (.118")
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm (.063")
Packaging Type	Tray
Pitch - Mating Interface	2.54mm (.100")
Pitch - Termination Interface	2.54mm (.100")
Temperature Range - Operating	-55°C to +125°C
Electrical	
Current - Maximum per Contact	1.5A
Data Rate	622.0 Mbps
Voltage - Maximum	250V AC (RMS)
Material Info	
Reference - Drawing Numbers	
Sales Drawing	SDA-85001-0001, SDA-85001-0476

EU RoHS

China RoHS

Compliance Status

Not Reviewed

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com

For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

85001Series

Mates With

85040 , 85050

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION