




SAK 10




SAK 16




SAK 35N




SAK 35



SAK 70



SAK 95N



Single Level

Single Level

Single Level

Single Level

Single Level

Single Level

0110060000* 0443760000*

0271060000* 0380660000*

0550660000 0608260000

0303560000 0380760000

0110080000* 0443780000*

0271080000* 0380680000*

0303580000 0380780000

0110020000 0443720000

0271020000 0380620000

0110070000 0443770000

0110030000

0271030000

0550630000

0303530000

0555760000 0608360000

0476560000 0582460000

0139160000

0555720000 0608320000

0476520000

0340820000

0550520000 0662220000

0370870000

0662270000

0608370000

0555730000

0340830000

0553860000*

0353160000*

10/40/51.5 (.40/1.58/2.07)

12/50/57.5 (.47/1.97/2.26)

16/58/67.5 (.63/2.28/2.66)

18/58/67.5 (.71/2.28/2.66)

22/75/79.5 (.87/2.95/3.13)

28/83.5/100.5 (1.1/3.3/3.96)

10/45/44 (.39/1.77/1.73)

12/50/50 (.47/1.97/1.97)

16/63/60 (.63/2.48/2.36)

18/58/60 (.71/2.28/2.36)

22/75/87 (.87/2.95/3.42)

28/83.5/96.5 (1.1/3.29/3.8)

12 (.47)

15 (.59)

18 (.71)

20 (.77)

24 (.94)

30 (1.18)

600 V / 60 A / #14...6 AWG

600 V / 80 A / #12...4 AWG

600 V / 100 A / #12...2 AWG

600 V / 105 A / #6...2 AWG

600 V / 150 A / #4...2/0 AWG

600 V / 195 A / #6...3/0 AWG

600 V / 65 A / #14...6 AWG

600 V / 87 A / #10...4 AWG

600 V / 145 A / #6...2 AWG

600 V / 150 A / #4...2/0 AWG

800 V / 57 A / 10 mm²

800 V / 76 A / 16 mm²

750 V / 135 A / 35 mm²

750 V / 135 A / 35 mm²

750 V / 207 A / 70 mm²

750 V / 250 A / 95 mm²

3.0 (26.5)

3.0 (26.5)

6.0 (53.0)

6.0 (53.0)

6.0 (53.0)

15 (200)

4

4

6

6

8

10

Type Part No.

Type Part No.

Type Part No.

Type Part No.

Type Part No.

Type Part No.

AP (1.5) 0117960000

AP (1.5) 0271160000

AP (1.5) 0303660000

AP (1.5) 0303660000

AP (2.0) 0340960000

AP (1.5) 0117980000

AP (1.5) 0271180000

AP (3.0) 0303680000

AP (3.0) 0303680000

AP (3.0) 0340920000

AP (3.0) 0550920000

AP (1.5) 0117920000

AP (3.0) 0271120000

AP (3.0) 0303620000

AP (3.0) 0303620000

AP (4.0) 0340930000

AP (3.0) 0550970000

AP (1.5) 0117970000

AP (3.0) 0271130000

AP (3.0) 0303670000

AP (3.0) 0303670000

AP (4.0) 0340930000

AP (1.5) 0117930000

AP (3.0) 0271130000

AP (3.0) 0303630000

AP (3.0) 0303630000

TW (1.5) 0130160000

TW (1.5) 0303660000

TW (1.5) 0304360000

TW (1.5) 0304360000

TW (1.5) 0130180000

TW (3.0) 0303680000

TW (1.5) 0130120000

TW (3.0) 0281120000

TW (3.0) 0304320000

TW (3.0) 0304320000

TW (1.5) 0130170000

TW (1.5) 0130130000

TW (3.0) 0281130000

TW (3.0) 0304330000

TW (3.0) 0304330000

TW (1.5) 0197100000

TW (2.0) 0607000000

TSch 1 0319160000

TSch 1 0319160000

Q 2 0457100000

Q 2 0457500000

QL 2 0564900000

QL 2 0123600000

QL 2 0345300000

QL 2 0551200000

Q 3 0457200000

Q 3 0457600000

QL 3 0565000000

QL 3 0123700000

QL 3 0167000000

Q 4 0457300000

Q 4 0457700000

QL 4 0565100000

QL 4 0123800000

Q 10 0457400000

Q 10 0457800000

QL 10 0565200000

QL 10 0338600000

VH 17 0267000000

VH 17 0267000000

VH 30.5 0345500000

VH 35 0551100000

BS M 4 x 30 0267100000

BS M 4 x 30 0267100000

BS M 5 x 45 0345600000

BS M 5 x 50 0630200000

SS M 4 0136400000

SS M 4 0136400000

SS M 5 0346100000

VL 2 0135900000

VL 2 0135800000

VL 2 0124000000

VH 19 0285100000

VH 19 0285100000

VH 24.5 0298700000

BS M 3 x 25 0292500000

BS M 3 x 25 0292500000

BS M 4 x 35 0298900000

AD 4 0178600000

AD 4 0518200000

AD 4 0576700000

AD 4 0178700000

AD 3 0669000000

BSK M 3 x 22 0128900000

BSK M 3 x 22 0128900000

BSK M 4 x 32 0129100000

BSK M 4 x 32 0129100000

BSK M 5 x 45 0344400000

ADP 2 0485300000

ADP 3 0485400000

ADP 3 0485400000

ADP 3 0485400000

ADP 3 0485400000

ADP 3 0485400000

HP 2 0485660000

HP 3 0485760000

HP 3 0485760000

HP 3 0485760000

HP 3 0485760000

HP 3 0485760000

DEK 5/5 0473460001

DEK 5/5 0473460001

DEK 5/5 0473460001

DEK 5/5 0473460001

DEK 5/5 0473460001

DEK 5/5 0473460001

DEK 5/5 0473560001

DEK 5/5 0473560001

DEK 5/5 0473560001

DEK 5/5 0473560001

DEK 5/5 0473560001

DEK 5/5 0473560001

*Touch-safe with DP cover.