




3.5mm Stereo Phone Plug

171-3301

KOBI CONN

3.5mm Stereo Phone Plug

171-3301



Dimensions: mm (In.)

SPECIFICATIONS	
Type:	3.5 mm stereo phone
Insulation resistance:	100MΩ min. @ 500VDC
Contact resistance:	50mΩ max.
Breakdown voltage:	500VAC for 1 minute
Temperature rating:	135°C
Contacts A & B, sleeve:	BSBM
Insulators A & B:	duracon
Insulators C & D:	polycarbonate
Terminals:	steel
Handle:	brass
Insulator E & cable protector:	PVC
Thread size:	M8 x PL

Date Last Revised: 4-18-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300535

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[171-3301](#)