


HEYClip™ Wire and Cable Holders

Vertical Orientation, Top Entry - For Panels up to .08" (1,9 mm) Thick*

- Gather and direct single or bundles of cable at low cost.
- **Two orientations:**
 1. Vertical for top entry and narrow width.
 2. Horizontal for side entry and low height where clearance is a problem.
- **Two gate types:**
 1. Regular gate secures cables with tension alone.
 2. Latch gate locks cables in place.
- Both types install with fingertip pressure into a 3/16" (4,8 mm) diameter mounting hole.
- Bayonet mount self-adjusts to various panel thickness up to .090" (2,3 mm).

WIRE CAPACITY		PART NO.		DESCRIPTION	FOOTPRINT		OVERALL HEIGHT C		MOUNTING HOLE DIA.	
		Natural	Black		in.	mm.	in.	mm.	in.	mm.
Regular Gate										
.437 x .171	11,1 x 4,3	3600	3600B	CH R-12	.22 x .60	5,6 x 15,2	.48	12,3	.187	4,8
.437 x .390	11,1 x 9,9	3605	3605B	CH R-18	.22 x .60	5,6 x 15,2	.72	18,2		
.437 x .750	11,1 x 19,1	3610	3610B	CH R-27	.22 x .60	5,6 x 15,2	1.06	27,0		
.437 x 1.062	11,1 x 26,9	3615	3615B	CH R-35	.22 x .60	5,6 x 15,2	1.38	35,0		
Latch Gate										
.437 x .134	11,1 x 3,4	3620	3620B	CH L-12	.22 x .60	5,6 x 15,2	.48	12,2	.187	4,8
.437 x .366	11,1 x 9,3	3625	3625B	CH L-18	.22 x .60	5,6 x 15,2	.72	18,3		
.437 x .721	11,1 x 18,3	3630	3630B	CH L-27	.22 x .60	5,6 x 15,2	1.07	27,2		
.437 x 1.037	11,1 x 26,3	3635	3635B	CH L-35	.22 x .60	5,6 x 15,2	1.39	35,3		


Standard colors natural and black.
*.28" (7,1 mm) bayonet length.



Horizontal Orientation, Side Entry - For Panels up to .09" (2,3 mm) Thick*

WIRE CAPACITY		PART NO.		DESCRIPTION	FOOTPRINT		OVERALL HEIGHT		MOUNTING HOLE DIA.	
in.	mm.	Natural	Black		A x B	C	in.	mm.	in.	mm.
Regular Gate										
.437 x .750	11,1 x 19,1	3652	3652B	CH R-27-90	.22 x 1.00	5,6 x 25,4	.62	15,9	.187	4,8
.437 x 1.062	11,1 x 26,9	3667	3667B	CH R-35-90	.22 x 1.33	5,6 x 33,8				
Latch Gate										
.437 x .718	11,1 x 18,3	3697	3697B	CH L-27-90	.22 x 1.00	5,6 x 25,4	.66	16,7	.187	4,8
.437 x 1.031	11,1 x 26,2	3712	3712B	CH L-35-90	.22 x 1.33	5,6 x 33,8				

Standard colors natural and black.
*.29" (7,4 mm) bayonet length.



Quick
Specs

Material: Nylon 6/6
Certifications: Recognized under UL File E54523 (vertical orientation parts only)
Flammability Rating: 94V-2
Material Temperature Index: 185°F (85°C)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[3848](#) [3882](#) [3884](#)