

Heavy Duty RTD Thermometer

Precision measurements to 0.01° over wide Temperature ranges

Features:

- Wide °F/°C measurements from -199.99 to 1562.0°F (-199.99 to 850.0° C)
- Selectable 0.1° or 0.01° display resolution
- Large 0.5" (13mm) 4-1/2 digit (20,000 count) LCD display
- Accurate to $\pm(0.1\% \text{ reading} + 0.4^\circ)$ under 200°F and $\pm(0.1\% \text{ reading} + 1.0^\circ)$ over 200°F
- Built-in linearity correction with fast response
- Sampling time of 0.4 second
- Data Hold to freeze the displayed value
- Built-in RS-232 PC serial interface with optional Data Acquisition software
- Accepts 4 wire Pt-100Ω RTD probes with DIN connector
- Dimensions: 7.1x2.8x1.3" (180x72x32mm)
Weight: 10oz (285g)
- Complete with protective rubber holster and 9V battery
- Probes are sold separately



**Optional
PC Software**



Ordering Information:

407907Heavy Duty RTD Thermometer
407907-NISTHeavy Duty RTD Thermometer w/ NIST Certificate
850187RTD probe w/ DIN plug, -200° to 500°C
850186RTD Stainless steel Surface probe
850189RTD Stainless steel Air probe, -200° to 400°C
156119117V AC adaptor
156121220V AC adaptor
407001Data Acquisition software program and cable
140001Hard vinyl carrying case

EXTECH INSTRUMENTS CORPORATION
285 Bear Hill Road, Waltham, MA 02451-1064, U.S.A.
Phone: 781-890-7440 • FAX 781-890-7864

ISO 9001:2000 CERTIFIED

Make mine an Extech!
www.extech.com



08/05/04 - R1

Copyright © 2004 Extech Instruments Corporation. All rights reserved including the right of reproduction in whole or in part in any form.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Extech:

407907-NIST 407907