



T120R0UVC2

Heavy Duty Cable Tie, 15.2" Long, 120lb Tensile Strength, PA66UV, Black, 100/pkg

Article Number: 111-00400

Part Number: T120R0UVC2

Type: T120R



Base Data

Part No.	T120R0UVC2
Type	T120R
Color	Black (BK)
Features	• UV stabilized heavy duty cable ties contain an inhibitor which prolongs the life of the tie in UV exposures . • Head design provides high tensile strength with very low insertion force. • Bent tail ensures a quick and simple installation.
Application Method	Quick, simple fixing by hand or with HellermannTyton tensioning tools
Identification Plate Position	none
Releasable Closure (Yes/No)	No
Tie Closure	plastic pawl
Typical Application	Used to bundle and secure wire and cable.
Variant	Inside Serrated

Product Dimensions

Min. Tensile Strength	120.0lbs / 535.0N
Length (L)	15.2" / 387.0mm
Width (W) (imperial)	0.3"
Width (W)	7.6mm

Min. Ø Bundle	0.2" / 5.0mm
Max. Ø Bundle	4.1" / 105.0mm
Thickness	1.8mm

Material and Specifications

Material	Polyamide 6.6 UV-stabilized (PA66UV)
US MILSPEC	MS3367-3-0
CSA Certified	No
Flammability	UL94 V2
Material Specification	HF
Operating Temperature	-40 °F to +185 °F (-40 °C to +85 °C)
ROHS Conformity	 RoHS
Specification	MIL 53421
UL Listed (US and Canada)	No
UL Recognized (US and Canada)	No

Logistic and Packaging

Packaging Type	bag
Pkg. Qty.	100
Carton Qty.	1000
EAN code	4031026274348
UPC	089306249986