

# Double Row Terminal Blocks

## 100 Series

## Kulka® 670A GP Series

## 300 Volts AC/DC (Class B)



106 / 670A GP 06

### Specifications:

- Base, General Purpose Phenolic, 150°C (UL RTI)
- Closed Back Design
- Screws, #6-32 Binder Head, Phil-Slot, Steel
- Terminals, Plated Brass
- 1-36 Poles
- 3/8" Centers
- Wire Range With Wire Binding Screw  
#12 - #22 AWG – 20 Amps
- Wire Range With Sems Pressure Screw #18 - #22 AWG  
Stranded Copper Wire Only, 150 Volts 15 Amps
- UL Recognized File No. XCFR2.E62806
- CSA Certified File No. LR19766
- **CE**
- RoHS Compliant

| MSP<br>Catalog # | Kulka®<br>Catalog # | # of poles | Dimensions |       |
|------------------|---------------------|------------|------------|-------|
|                  |                     |            | A          | B     |
| 101              | 670A GP 01          | 1          | 1.03       | 0.75  |
| 102              | 670A GP 02          | 2          | 1.41       | 1.13  |
| 103              | 670A GP 03          | 3          | 1.78       | 1.50  |
| 104              | 670A GP 04          | 4          | 2.16       | 1.88  |
| 105              | 670A GP 05          | 5          | 2.53       | 2.25  |
| 106              | 670A GP 06          | 6          | 2.91       | 2.63  |
| 107              | 670A GP 07          | 7          | 3.28       | 3.00  |
| 108              | 670A GP 08          | 8          | 3.66       | 3.38  |
| 109              | 670A GP 09          | 9          | 4.03       | 3.75  |
| 110              | 670A GP 10          | 10         | 4.41       | 4.13  |
| 111              | 670A GP 11          | 11         | 4.78       | 4.50  |
| 112              | 670A GP 12          | 12         | 5.16       | 4.88  |
| 113              | 670A GP 13          | 13         | 5.53       | 5.25  |
| 114              | 670A GP 14          | 14         | 5.91       | 5.63  |
| 115              | 670A GP 15          | 15         | 6.28       | 6.00  |
| 116              | 670A GP 16          | 16         | 6.66       | 6.38  |
| 117              | 670A GP 17          | 17         | 7.03       | 6.75  |
| 118              | 670A GP 18          | 18         | 7.41       | 7.13  |
| 119              | 670A GP 19          | 19         | 7.78       | 7.50  |
| 120              | 670A GP 20          | 20         | 8.16       | 7.88  |
| 121              | 670A GP 21          | 21         | 8.53       | 8.25  |
| 122              | 670A GP 22          | 22         | 8.91       | 8.63  |
| 123              | 670A GP 23          | 23         | 9.28       | 9.00  |
| 124              | 670A GP 24          | 24         | 9.66       | 9.38  |
| 125              | 670A GP 25          | 25         | 10.03      | 9.75  |
| 126              | 670A GP 26          | 26         | 10.41      | 10.13 |
| 127              | 670A GP 27          | 27         | 10.78      | 10.50 |
| 128              | 670A GP 28          | 28         | 11.16      | 10.88 |
| 129              | 670A GP 29          | 29         | 11.53      | 11.25 |
| 130              | 670A GP 30          | 30         | 11.91      | 11.63 |
| 131              | 670A GP 31          | 31         | 12.28      | 12.00 |
| 132              | 670A GP 32          | 32         | 12.66      | 12.38 |
| 133              | 670A GP 33          | 33         | 13.03      | 12.75 |
| 134              | 670A GP 34          | 34         | 13.41      | 13.13 |
| 135              | 670A GP 35          | 35         | 13.78      | 13.50 |
| 136              | 670A GP 36          | 36         | 14.16      | 13.88 |

mm=dim X 25.4


### Hardware Options:

(Hardware options may affect ratings - consult Customer Service)

| CATALOG # | PRODUCT  | PAGE                          |
|-----------|----------|-------------------------------|
| MSP       | KULKA    | REFERENCE                     |
| F1        | KT19     | Full Quick Connect (0° Flat)  |
| F2        | KT20     | Full Quick Connect (45° Bend) |
| F3        | KT21     | Full Quick Connect (90° Bend) |
| HF1       | KT25     | Half Quick Connect (0° Flat)  |
| HF2       | KT26     | Half Quick Connect (45° Bend) |
| HF3       | KT27     | Half Quick Connect (90° Bend) |
| S         | ST       | Full Solder                   |
| HS        | 3/4 ST   | Half Solder                   |
| L         | Y        | Feed Thru Solder (.312)       |
| LSL       | YSY      | Feed Thru Solder (.500)       |
| LL 100    | J 600    | Line to Line Jumper           |
|           | 600RJ(S) | Multiple Position Jumper      |
| LWW       | 3000     | Feed Thru Wire Wrap (.593)    |
| PSB       |          | Phil-Slot Brass Screw         |

Quick Connects: .020" x .187"

See pages 104-115 for terminal block accessories



For electronic drawings or 2D/3D  
CAD data, submit request at  
[www.marathonsp.com/drawings.html](http://www.marathonsp.com/drawings.html)