



NOTES:

1. ALL DIMENSION IN MM [INCH]
2. GENERAL TOLERANCE: $X.X = \pm 0.4$
 $X.XX = \pm 0.25$
3. TERM. NOS. FOR REF. ONLY
4. CONTACT RATING SWITCHING: 150mA, 250V AC/DC
350mA, 110V AC/DC
5. CONTACT RATING (NON-SWITCHING) 5A
6. OPERATING FORCE: 425 $\pm$ 100 CM/STANDARD
7. OPERATING TEMP: -30 $^{\circ}$ to 85 $^{\circ}$ C
8. CIRCUIT SP: 2 POSITIONS, 60 $^{\circ}$ INDEX.
9. DIELECTRIC STRENGTH 1000V RMS min. @ SEA LEVEL
10. DESIGNATE MAJOR DIMENSIONS
11. HARDWARE SUPPLIED ON SWITCH - SEE BELOW
STOP RING, LOCKWASHER, & HEXNUT




CONTACT CONFIGURATION

TIMING: (BBM) Non-Shorting



TERMINATION DETAIL

SCALE 2X



E-SWITCH®				
TITLE KC-53-A-(30.0mm) 01-N-L-S				
SCALE 1.5:1		DATE 2/27/03	DR CJB	DWG G527551
REV A				
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED				
B				
A	12855	RELEASED FOR PRODUCTION	2/27/03	CJB
REV.	ECN No.	DESCRIPTION	DATE	CHKD