



Wobble extensions


*Inaccessible with a socket or a universal joint?
Use a wobble extension!*



R.S 1/4" drive wobble extensions

- Square drive profile gives 6° working angle.

	B mm	D mm	L mm	ΔΔ g
R.209S	8,2	12	55	30
R.210S	8,2	12	100	45




R 1/4" drive flexible extension 150 mm

R.216

- Reaches fasteners out of direct access line.
- Unsuitable for high torques : max. 2.8 N.m.

ΔΔ : 66 g.




1/4" universal joint

R.240A

- ▷ Performance : to ISO 3316, DIN 3123, NF ISO 3316.
- Spring-stiffened joints. Stays in position when reaching for fasteners.

- Significant time savings.

ΔΔ : 20 g.



1/4" to 3/8" coupler

R.232

- 1/4" female to 3/8" male square drive.
- For adapting 3/8" drive sockets.

ΔΔ : 16 g.

