



GROOVE JOINT PLIER

Strong, drop-forged tempered steel pliers hold and turn work of various sizes. Rust resistant polished chrome finish. Comfortable bonded vinyl grip.

Product ID No.	Length		Box/Ctn
	in	mm	
84-137	7	180	6 / 36
84-139	10	250	6 / 36
84-140	12	305	4 / 24



LINESMAN PLIER

Serrated jaw provide grip and leverage on heavy duty applications. Finely honed cutting edges cut most types of wire. Tempered alloy steel for strength and durability. Rust resistant protective finish. Comfortable bonded vinyl grip.

Product ID No.	Length		Box/Ctn
	in	mm	
84-150	7	180	6 / 36
84-151	8	203	6 / 36



FINE WOODWORKING CARPENTER'S NIPPERS

For removing and cutting nails. The beveled cutting edge are over 1" wide and machined to a smooth curved surface to protect your work surface when extracting a nail. Forged from high carbon steel, hardened and tempered for long life. The pivots and joints are precision machined for accuracy.

Product ID No.	Length		Box/Ctn
	in	mm	
84-185	9-3/4	245	6 / 30



PLIER

A handy tool that cuts electrical wire, strip insulation, shears screws and bolts clean, crimps terminals. Plus a plier for many more uses. All the action is up front, safely out of the way of hands and fingers. Pliers cut 4-40, 6-32, 8-32, 10-24 and 10-32 size threads.

Product ID No.	Overall Length		Box/Ctn
	in	mm	
84-203	8-1/2	215	6 / 36

WARNING: Grips do not protect against electrical shock.



WIRE STRIPPER

Cuts and strips wire from 10 to 26 gauge. Adjustable slide stop and hole for bending and looping wire. Rust resistant finish. Comfortable vinyl grips.

Product ID No.	Box/Ctn
84-213	5 / 50



2 PIECE PLIER AND WRENCH SET

Set includes 6" slip joint plier and 8" adjustable wrench. Quality tools for the most common fastening and holding jobs around home, shop and garage.

Product ID No.	Contents	Box/Ctn
90-474	84-106 6" Slip Joint Plier 84-368 8" Adjustable Wrench	4 / 24



THE "CLAW" ADJUSTABLE WRENCH

■ Grips fastener on four sides — won't slip off. Moveable jaw has precision adjustment and won't slip like conventional adjustable wrenches. Handle is investment cast for strength. Packaged in a blister card.

Product ID No.	Length		Box/Ctn
	in	mm	
87-454	6	150	6 / 36
87-455	8	200	6 / 36
87-458	10	250	6 / 24



ADJUSTABLE WRENCH

Strong tempered steel chrome vanadium steel wrench for fastening or holding nuts and bolts in shop or home. Precision machined screw for smooth jaw adjustment. Rust resistant polished chrome finish. Handy hang hole for wall storage.

Product ID No.	Length		Box/Ctn
	in	mm	
87-366	6	152	6 / 36
87-368	8	203	6 / 36
87-470	10	250	6 / 36
87-472	12	305	4 / 24



WARNING: WORK SAFELY WITH TOOLS
WEAR SAFETY GOGGLES.