



Bud Industries, Inc.

# QUALITY ENCLOSURES

Accessories - Power Outlet  
Strips

## Surge Supressed Power Outlet Strip



### ***Design Features***

Provides protection to data or word processing equipment and other sensitive electrical equipment from sudden spikes or high energy voltage. Prevents equipment damage, lost or distorted data. Maximum surge current is 13000 amps, response time is < 5ns. 15 amp thermal type, circuit breaker with reset. 14 gauge, 3 wire, 6 foot power cord, all components U. L. approved.

| Surge Suppressed Power Outlet Strips |  |                |        |             |
|--------------------------------------|--|----------------|--------|-------------|
| Catalog Number                       |  | No. of Outlets | Length | Weight Lbs. |
| POS-4-S                              |  | 4              | 17.50" | 2.00        |
| POS-66                               |  | 6              | 12.25" | 1.75        |
| POS-7-S                              |  | 7              | 48.00" | 3.50        |
| POS-9-S                              |  | 9              | 60.00" | 4.25        |
| POS-11-S                             |  | 11             | 72.00" | 4.75        |

PART  
NAME

## POWER OUTLET STRIP

PART  
No.

POS-4-S TO POS-66

14 GAUGE 3 WIRE POWER CORD  
6 FOOT LONGMOLDED ON 3-PRONG PLUG  
15 AMP 125 VOLT

STRAIN RELIEF

GROUNDING TYPE 15 AMP 125 VOLT  
RECEPTACLE

1.062

1.062


H

SURGE PROTECTION  
INDICATOR LAMP  
15 AMP 125 VOLT

D TYP.

C

B

ILLUMINATED  
ON/ OFF SWITCH  
15 AMP 125 VOLTCIRCUIT BREAKER THERMAL TYPE  
15 AMP 125 VOLT  
WITH RESET




E

F

0.188

HOUSING

0.125

MATERIAL:HOUSING (TOP & BOTTOM CHANNELS) &  
MTG. CLIPS - ALUMINUM EXTRUSIONS  
END CAPS - ABS PLASTICFINISH:HOUSING - GREY  
- PUTTY WHITE (POS-66 ONLY)  
RECEPTACLES, POWER CORD & END  
CAPS - BLACK  
- PUTTY WHITE (POS-66 ONLY)  
MTG. CLIPS - NATURALMOUNTING CLIP DETAIL

| PART NO. | QTY. OF<br>OUTLETS | SURGE<br>SUPPRESSED | A      | B     | C                            | D     | E     | F     | G     | H     | QTY. OF<br>MTG. CLIPS |
|----------|--------------------|---------------------|--------|-------|------------------------------|-------|-------|-------|-------|-------|-----------------------|
| POS-4-S  | (4)                | YES                 | 17.625 | 0.938 | (3) SPACES @ 3.062 = 9.188   | 3.062 | 2.000 | 1.750 | 2.093 | 2.000 | (2)                   |
| POS-6    | (6)                | NO                  | 12.250 | 0.969 | (5) SPACES @ 1.250 = 6.250   | 1.250 | 1.828 | 1.563 | 1.843 | 1.750 | (2)                   |
| POS-7-S  | (7)                | YES                 | 48.125 | 4.625 | (6) SPACES @ 6.000 = 36.000  | 6.000 | 2.000 | 1.750 | 2.093 | 2.000 | (2)                   |
| POS-9-S  | (9)                | YES                 | 60.125 | 4.625 | (8) SPACES @ 6.000 = 48.000  | 6.000 | 2.000 | 1.750 | 2.093 | 2.000 | (3)                   |
| POS-11-S | (11)               | YES                 | 72.125 | 4.625 | (10) SPACES @ 6.000 = 60.000 | 6.000 | 2.000 | 1.750 | 2.093 | 2.000 | (3)                   |
| POS-66   | (6)                | YES                 | 13.000 | 0.969 | (5) SPACES @ 1.250 = 6.250   | 1.250 | 2.000 | 1.750 | 2.093 | 2.000 | (2)                   |