


HEX NYLON TAPPED SPACERS

561-L4.25, 561-L4.375, 561-L4.50, 561-L4.75, 561-L41.0, 561-L6.25, 561-L6.375, 561-L6.50, 561-L6.75, 561-L61.0, 561-L8.25, 561-L8.375, 561-L8.50, 561-L8.75, 561-L81.0, 561-L4.875, 561-L6.875, 561-L8.875, 561-L4.625, 561-L6.625, 561-L8.625, 561-14HTSP023, 561-L61.5

Date Last Revised: 1/7/13

DIMENSIONS: in(mm.)



MOUSER STOCK NO.	Description	L	A	Tapped
561-L4.25	HTSP 1	0.250 (±.015)	0.250 (±.015)	4-40
561-L4.375	HTSP 2	0.375 (±.015)	0.250 (±.015)	4-40
561-L4.50	HTSP 3	0.500 (±.015)	0.250 (±.015)	4-40
561-L4.75	HTSP 4	0.750 (±.015)	0.250 (±.015)	4-40
561-L41.0	HTSP 5	1.000 (±.015)	0.250 (±.015)	4-40
561-L6.25	HTSP 6	0.250 (±.015)	0.250 (±.015)	6-32
561-L6.375	HTSP 7	0.375 (±.015)	0.250 (±.015)	6-32
561-L6.50	HTSP 8	0.500 (±.015)	0.250 (±.015)	6-32
561-L6.75	HTSP 9	0.750 (±.015)	0.250 (±.015)	6-32
561-L61.0	HTSP 10	1.000 (±.015)	0.250 (±.015)	6-32
561-L8.25	HTSP 11	0.250 (±.015)	0.250 (±.015)	8-32
561-L8.375	HTSP 12	0.375 (±.015)	0.250 (±.015)	8-32
561-L8.50	HTSP 13	0.500 (±.015)	0.250 (±.015)	8-32
561-L8.75	HTSP 14	0.750 (±.015)	0.250 (±.015)	8-32
561-L81.0	HTSP 15	1.000 (±.015)	0.250 (±.015)	8-32
561-L4.875	HTSP 16	0.875 (±.015)	0.250 (±.015)	4-40
561-L6.875	HTSP 17	0.875 (±.015)	0.250 (±.015)	6-32
561-L8.875	HTSP 18	0.875 (±.015)	0.250 (±.015)	8-32
561-L4.625	HTSP 19	0.625 (±.015)	0.250 (±.015)	4-40
561-L6.625	HTSP 20	0.625 (±.015)	0.250 (±.015)	6-32
561-L8.625	HTSP 21	0.625 (±.015)	0.250 (±.015)	8-32
561-14HTSP023	HTSP 23	1.250 (±.015)	0.250 (±.015)	6-32
561-L61.5	HTSP 36	1.500 (±.015)	0.250 (±.015)	6-32
RoHS Compliant				

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

EPD-200914

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Eagle Plastic Devices:

[561-L61.5](#) [561-L8.75](#) [561-L8.875](#) [561-L81.0](#) [561-L6.875](#) [561-L6.75](#) [561-14HTSP023](#) [561-L4.75](#) [561-L4.625](#) [561-L4.375](#) [561-L4.50](#) [561-L4.875](#) [561-L4.25](#) [561-L6.625](#) [561-L6.375](#) [561-L6.25](#) [561-L41.0](#) [561-L6.50](#) [561-L61.0](#) [561-L8.25](#) [561-L8.625](#) [561-L8.50](#) [561-L8.375](#)