




FEATURES:

- Connector One End only to allow customer modification.
- Lengths other than those specified are available upon request.

MATERIALS:

Conn: 1st End – BNC Male.

Finish: Body and Fittings, Tarnish Resistant.

Center Contact: Gold plated per requirements of MIL-C-39012.

Nominal Impedance: 50 Ohms.

Cable:

RG58C/U. (.195) O.D.

Marking: "POMONA 1661-C-XX".

50 Ohms Impedance

Conn: 2nd End – No connection.

RATINGS:

Voltage: Shield-Earth: 300VAC/60VDC Max.

Inner conductor – Shield: 500 VRMS Max.

ORDERING INFORMATION: Model 1661

Ordering Example: 1661-C-60 Indicates 60" (1524) in length

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ± .005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA