




Dimensions: mm (In.)



| POS.1 | POS.2 | POS.3 |
|-------------------------------------------------------------------------------------|-------|--------------------------------------------------------------------------------------|
| | | |
| ON | NONE | ON |
| 2-1, 5-4 | | 2-3, 5-6 |
|  | OPEN |  |

Switch Function

Electrical Specifications:

- Rating: 1A/250VAC
3A/120VAC or 28 VDC
- Contact Resistance: 50mΩ max. initial
- Insulation Resistance: 1000MΩ min.
- Dielectric Strength: 1000 V RMS @ sea level
- Breaking Capacity: 1A/250VAC
- Minimum Load: 100mA

Mechanical Specifications:

- Mechanical Life: 20,000 cycles
- Operating Temperature: -30°C to 85°C

Note:

- RoHS compliant

Materials:

- Case: Nylon, white
- Actuator: Nylon, black
- Housing: Nylon, black
- Contact: Silver plated copper alloy
- Terminals: Silver plated copper alloy

Miniature Slide Switch
103-5005-EV

Mountain
Switch

Available from Mouser Electronics

www.mouser.com 1-800-346-6873

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[103-5005-EV](#) [103-5005-EVX](#)