

datasheet for PK 10 A
article number: 930099100



product description:	order number: 930 099-100
description:	Pole terminal with claw edge and captive insulated head. 4 mm diameter nickel-plated brass threaded bolt with 2 mm diameter transverse hole. For installation in equipment chassis and switch panels.
typ:	PK 10 A schwarz/black
system:	4 mm system
order number:	930 099-100
color	
other color versions:	
technical data	
type of contact:	spring loaded socket
type of termination:	M 4 thread
rated voltage:	DC 60 V
rated current:	16 A
contact resistance:	2 mOhm
mounting:	screw
material	
contact material:	brass
contact surface material:	nickel-plated
housing material:	PF
environmental conditions:	
temperature range:	-25 °C to +100 °C
flammable class:	
housing:	94 V-0
drawing	