

**RoHS Compliant**



**PM-020/ PM-143**

**PCMCIA 1xRS232 1MBaud**

**"SERIAL CARDS ENGINEERED TO EXCEED EXPECTATIONS"**



#### Features

- 1 port RS232
- PCMCIA socket size
- 128 Byte Tx and 128 Byte Rx FIFOs
- Up to 921,600 Baud
- DB9 connector (9 Pin Male)
- Drivers for all popular operating systems
- Sample Programs, Test & Terminal software
- Lifetime Support
- Lifetime Warranty (registration required)

#### Options



PM-020:  
PCMCIA 1xRS232  
1MBaud

PM-143  
PCMCIA 1xRS232  
RUGGED 1MBaud



#### Description

PC Card providing one RS232 serial port. Up to 921,600 data transfer rates and the 128 byte deep transmit and 128 byte receive FIFOs, coupled with 1Mbit/s line drivers deliver uncompromising performance on your laptop.

Being mobile no longer limits your options. Standard and ruggedised card options to suit your needs.

With Brainboxes industry renowned Lifetime Warranty and Lifetime Support!

#### Software

Microsoft signed drivers (easy installation & robust operation) for:

- Windows 7 32 bit & 64 bit Editions
- Windows Vista 32 bit & 64 bit editions
- Windows XP 32 bit & 64 bit editions
- Windows 2000



As well as: full product documentation, a thorough troubleshooting guide and terminal software. Detailed sample source code for many popular programming languages. Further OS support on next page.



#### ORDER

##### Description

PCMCIA 1xRS232 1MBaud  
PCMCIA 1xRS232 RUGGED 1MBaud


##### Code

PM-020  
PM-143



## PCMCIA 1xRS232 1MBaud

PM-020/ PM-143: Full Specification

<b>Port</b>  	<b>Ports</b>  <b>Connector</b> <b>FIFO size</b> <b>Operating Distance</b> <b>Cable</b>	1 x RS232  DB9 connector -- 9 Pin Male  128 RX FIFO + 128 TX FIFO  EIA - RS232 Standard  Fully wired moulded cable
<b>Port Settings</b>  	<b>Baud Rate</b>  <b>Data Bits</b> <b>Parity</b> <b>Stop Bits</b> <b>Flow Control</b> <b>Tx/Rx Modes</b>	921,600  5,6,7 or 8  Odd, Even, None, Mark or Space  1, 1.5 or 2   Point to Point
<b>Interface</b>  	<b>OS Compatibility</b>         <b>BUS</b>	Microsoft Windows 7 Windows Vista 32 bit & 64 bit Editions Windows XP 32 bit & 64 bit Editions Microsoft Windows 2000      PCMCIA
<b>Approvals</b>  	<b>Other Approvals</b>  <b>Microsoft Approvals</b>	Microsoft Certified Gold Partner WEEE RoHS EMC: CE  Microsoft Certified Gold Partner Windows 7 32 bit & 64 bit Editions Windows Vista 32 bit & 64 bit editions Windows XP 32 bit & 64 bit editions Windows 2000
<b>General</b>	<b>PCB Layers</b>  <b>Power Consumption</b>   <b>Weight</b> <b>Size</b>	4  210mA @ 5V, 20mA @ 12V (PM-020) 210mA @ 5V , 20mA @ 12V (PM-143)  0.027 kg (PM-020) 0.05 kg (PM-143) Kg PCMCIA Type II: null
<b>Box Content</b>	<b>Packaging</b>  <b>Card</b>	Installation CD including manual, Microsoft signed drivers & utilities  PCMCIA 1xRS232 1MBaud Fully wired moulded cable
<b>Product Support</b>  	<b>Warranty</b>  <b>Support</b>	Lifetime (online registration required)  Lifetime Web, Email and Phone Support from fully qualified, friendly staff who work in and alongside the Product Development Team
<b>Additional</b>  	<b>OEM option</b>  <b>Made In</b>  <b>Customisable</b>	Available for bulk buy OEM  Manufactured in the UK by Brainboxes Winner 2005 European Electronics Industry Awards "Manufacturer of the Year" Brainboxes operate a "Perfect Fit Custom Design" policy for volume users. More Info: <a href="mailto:sales@brainboxes.com">sales@brainboxes.com</a>