




AD5010(8) SERIES

External Dimensions



Frame:Plastic(UL:94V-0)
Impeller:Plastic(UL:94V-0)
Lead wire:UL1007AWG26

Specifications(Nominal)


*:Noise is measured at the distance of one (1) meter from the axis of intake.

Bearing type: ◎=Ball ※=Sleeve ●=Hypro bearing

Frame size (mm)	Model No.	Bearing System Type	Rated Voltage (VDC)	Current (A)	Power (W)	Rated Speed (rpm)	Maximum AirFlow (CMM) (CFM)	Maximum Pressure (InAq) (mmAq)	*Noise Level (dB/A)	Weight (g)
50x50x10	AD0512LB-G70(8)	◎ ※ ●	12	0.08	0.96	3900	0.254 9.000	0.060 1.524	20.0	18.0
	AD0512MB-G70(8)	◎ ※ ●	12	0.09	1.08	4600	0.294 10.400	0.100 2.540	25.0	
	AD0512HB-G70(8)	◎ ※ ●	12	0.12	1.44	5200	0.316 11.000	0.120 3.048	28.0	
	AD0524LB-G70(8)	◎ ※ ●	24	0.05	1.20	3900	0.237 8.400	0.070 1.778	21.0	
	AD0524MB-G70(8)	◎ ※ ●	24	0.06	1.44	4600	0.294 10.400	0.100 2.540	25.0	
	AD0524HB-G70(8)	◎ ※ ●	24	0.08	1.92	5200	0.311 11.000	0.120 3.048	28.0	

Specifications subject to change without notice.

The specification for bearing type is for reference only , for more bearing types information, please contact with your ADDA sales representative, thanks!!
(網頁上呈現產品軸承資訊均以2Ball為主，若需其他產品資訊請聯絡您在ADDA的業務代表，謝謝！！)



*Motor protective circuit and third lead wire functions

0	1	2	3	4	6	7	8	9	A	B
✓	✓	✓	✓		✓					

*Safety approvals

✓	✓		✓	✓