

PRECISION POWER WIREWOUND RESISTORS SILICONE COATED 1/2 WATT TO 50 WATT

100 SERIES




World's widest range! 0.005Ω ~2MΩ, ±0.005% ~10%, 0.5W ~50W.
Low cost, available from stock & exclusive **SWIFT™** delivery program.

OPTIONS

- ☐ Option X: Low Inductance
- ☐ Option P: Increased Pulse Capability
- ☐ Option F: Flameproof Coating UL94V-0
- ☐ Option ER: 100-Hour Burn-In
- ☐ Option B: Increased Power
- ☐ Radial leads (opt.R), low thermal emf (opt.E), matched sets, custom marking, cut & form, Hi-Rel screening, non-standard values, high-voltage, etc. Customized components are RCD's speciality!

DERATING (derate W/V/A ratings when ambient temp >25°C):
Char. U is max. power for ±0.5% typ. operational life stability & 275°C hotspot;
Char. V is max. power for ±3% stability & 350°C hotspot



	RCD Type	MIL Type ⁵	Std. Wattage Ratings ¹⁰		Opt.B Wattage Ratings ¹⁰		Resistance Range ^{6,7}	Maximum Voltage Rating ^{1,6}	DIMENSIONS [Numbers in brackets are mm]			
			Char.U	Char.V	Char.U	Char.V			A ³	C ²	D ⁸ ± .003 [.08]	
											± .062	[1.58]
Stock	102	-	0.5	0.8	0.8	1.0	.01Ω - 2K	30V	.16 ±.03 [4 ±.8]	.07 ±.02[1.8 ±.5]	.020	-
	110	RW81 (110B)	0.8	1.0	1.5	2.0	.01Ω - 8K	40V	.24 ±.03 [6 ±.8]	.085 [2.16]	.020	.024 (opt. 22)
	115	-	1.0	1.2	1.5	2.0	.01Ω - 12K	45V	.312 [7.92]	.085 [2.16]	.020	.024 (opt. 22)
	120	-	1.0	1.2	-	-	.01Ω - 15K	50V	.344 [8.74]	.096 [2.44]	.020	.024 (opt. 22)
	125	RW70 (125B RW80)	1.5	1.8	2.0	2.5	.01Ω - 20K	55V	.385 [9.78]	.096 [2.44]	.020	.024 (opt. 22)
Stock	130	-	1.6	2.0	-	-	.01Ω - 22K	65V	.530 [13.5]	.096 [2.44]	.020	.024 (opt. 22)
	133	-	2.0	3.0	3.0	4.0	.005Ω - 20K	80V	.355 [9.00]	.156 [3.96]	.031	.024 (opt. 22)
	135	RW69	3.0	4.0	4.0	5.0	.005Ω - 40K	140V	.500 [12.7]	.188 [4.78]	.031	.024(22), .040(18)
	140	RW79	3.0	4.0	4.0	5.0	.005Ω - 50K	140V	.550 [14.2]	.188 [4.78]	.031	.040 (opt. 18)
	145	-	3.5	4.5	4.5	6.5	.005Ω - 60K	180V	.770 [19.6]	.188 [4.78]	.031	.040 (opt. 18)
Stock	150	-	3.5	4.5	5.0	7.0	.005Ω - 60K	150V	.500 [12.7]	.225 [5.72]	.040	.032 (opt. 20)
	155	-	4.0	5.0	6.0	8.0	.005Ω - 100K	210V	.625 [15.9]	.225 [5.72]	.040	.032 (opt. 20)
	156	-	5.0	6.0	-	-	.005Ω - 150K	300V	.800 [20.3]	.250 [6.35]	.040	.032 (opt. 20)
	160	RW74	5.0	7.0	7.0	10	.005Ω - 200K	400V	.875 [22.2]	.312 [7.92]	.040	.032 (opt. 20)
	165	RW67	6.0	7.5	-	-	.005Ω - 220K	450V	1.000 [25.4]	.312 [7.92]	.040	.032 (opt. 20)
Stock	170	-	7.0	9.0	10	12	.005Ω - 300K	550V	1.200 [30.9]	.312 [7.92]	.040	.032 (opt. 20)
	171	-	7.0	8.5	-	-	.005Ω - 250K	700V	1.660 [42.2]	.208 [5.28]	.031	.040 (opt. 18)
	172	-	8.5	10	-	-	.005Ω - 400K	900V	2.100 [53.3]	.225 [5.72]	.031	.040 (opt. 18)
	173	-	9.0	11	12	14	.005Ω - 400K	650V	1.550 [39.4]	.300 [7.62]	.040	.032 (opt. 20)
	175	RW68, 78	10	13	15	18	.005Ω - 500K	900V	1.720 ⁴ [43.7]	.350 ⁴ [8.89]	.040	.032 (opt. 20)
	176	-	10	12	-	-	.005Ω - 500K	800V	1.875 [47.6]	.300 [7.62]	.040	.032 (opt. 20)
	178	-	13	15	-	-	.01Ω - 750K	1150V	2.410 [61.2]	.350 [8.89]	.040	.032 (opt. 20)
	180	RW56	14	16	16	20	.01Ω - 800K	1000V	2.100 [53.3]	.500 [12.7]	.040	-
	185	-	20	25	-	-	.015Ω - 1M	1350V	2.800 [71.1]	.500 [12.7]	.040	-
	186	-	25	30	-	-	.010Ω - 1M	1400V	4.060 [103]	.350 [8.89]	.040	.032 (opt. 20)
	190	-	40	50	-	-	.025Ω - 2M	1500V	5.000 [127]	.500 [12.7]	.040	-

¹ Working voltage=(PR)^{1/2}, not to exceed max rating (multiply by 0.7 for Opt.X) ² Allow .032" additional for Opt X, Opt 33, or values <1Ω ³ Coating overflow onto each lead ≤2x D typ ⁴ Performance is typical for Char.U with tol ≤1%, & is dependent on resis, options, etc. Consult factory for Char.V & tol >1% ⁵ Military p/n's are given for reference only & do not imply qualification or exact interchangeability ⁶ Increased range avail ⁷ Resis value measured at 3/8" ±1/16" from each end of body ⁸ Heavier lead gauge option is recommended on low values to enable lower leadwire resis, increased current, & improved TC ⁹ Lead length applies to bulk packaged units (taped parts generally have shorter leads, refer to taping spec.) ¹⁰ Series 100 has dual power rating depending on temp. rise & stability requirements; derate 50% to ensure high reliability & operational life stability

TYPICAL PERFORMANCE ⁴

Operational Life (Char.U)	±0.5% (±1% on Opt.B & sizes ≥10W)
Thermal Shock	±0.2%
Moisture Resistance	±0.2%
Shock and Vibration	±0.1%
Overload, 5 Sec	5x rated W 102-156, 10x W 160-190
Dielectric Strength: type 102-130	300V (for 500V specify opt.23)
Dielectric Strength: type 133-190	500V (for 1KV specify opt.33)
Max. Current (not to exceed wattage or voltage rating)	Resistors with .020" lead dia = 11A, .024" = 15A, .032" = 22A, .040" = 30A
TCR: temp coefficient of resistance element, tol ≤1% (contact factory >1%)	≥10Ω 20ppm (5 & 10ppm avail.) 1-9.9Ω 50ppm (10, 20, 30ppm avail.) 0.1-.99Ω 90ppm (20, 30, 50 ppm avail.) 0.01-.099Ω 300ppm (50, 100, 200ppm avail.) 0.1Ω -.049Ω 600ppm (100, 200, 300ppm avail.)

P/N DESIGNATION:

135 ☐ - **102** - **J** **B** ☐ **W**

RCD Type _____

Options: X, R, V, P, F, ER, E, B, 76, 75, 33, 22, 20, 18 (leave blank if standard)

Resis. Code 1% & tighter tols: 3 signif. digits & multiplier, e.g. R100= 0.1Ω, 1R00= 1Ω, 1000= 100Ω, 1001= 1KΩ.

2%-10%: 2digits & multiplier (R10= .1Ω, 1R0=1Ω, 100=10Ω, 102=1K). Use extra digits as needed: R005, R0075, R012, etc.

Tolerance: K=10%, J=5%, H=3%, G=2%, F=1%, D=0.5%, C=0.25%, B=0.1%, A=0.05%, Q=0.02%, T=0.01%, V= .005%

Packaging: B= Bulk, T= T&R (avail. on type 102 to 176)

Optional TC: 5= 5ppm, 10= 10ppm, 20= 20ppm, 30= 30ppm, 50= 50ppm, 101= 100ppm, 201=200ppm (leave blank if std)

Termination: W=RoHS (std), Q= Tin/Lead (leave blank if both acceptable)

RCD Components Inc, 520 E.Industrial Park Dr, Manchester, NH, USA 03109 rccdcomponents.com Tel: 603-669-0054 Fax: 603-669-5455 Email: sales@rccdcomponents.com

FA039H Sale of this product is in accordance with GF-061. Specifications subject to change without notice.