

Product Description

Sealed polyester swabs

Very clean and durable all-purpose swabs.


An exceptionally clean swab produced by Ideal-tek's proprietary process of thermoforming and welding the swab head. Featuring either knit or nonwoven fabric heads, these swabs are acid and solvent resistant. Sealed edges build in high strength with no loose fibers or particulates. They are ideal for tough scrubbing around raised shapes. Class 10 (ISO Class 4) processing gives you the lowest ionic, non-volatile residue and particle contaminants.

Handle Material: polypropylene flexible

Head material: knit or non-woven polyester


Sale units: 1 bag of 125 swabs
1 box of 20 bags

IT38040 Mini polyester knitted



Swab length:	2.7"	6.9 cm
Handle width:	0.09"	2.3 mm
Head length:	0.44"	11.2 mm
Head thickness:	0.09"	2.4 mm
Head width:	0.12"	3.0 mm

IT38140 Mini polyester knitted



Swab length:	2.7"	6.9 cm
Handle width:	0.09"	2.3 mm
Head length:	0.48"	12.1 mm
Head thickness:	0.06"	1.6 mm
Head width:	0.12"	3.0 mm

IT38540 Mini polyester non woven



Swab length:	2.7"	6.9 cm
Handle width:	0.09"	2.3 mm
Head length:	0.46"	11.7 mm
Head thickness:	0.04"	1.0 mm
Head width:	0.12"	3.0 mm