


REVISIONS					
P	F	ZONE	DESCRIPTION	DATE	APPD
		LTR			
		B	REV & REDRAWN PER 0720-0040-93	3-29-93	1 st DAP


MEET RICO

DIMENSIONS LISTED IN mm (INCHES)



AMP WIRE RANGE	 E13288 Listed
22-16 AWG SOLID OR STRANDED	22-16 AWG SOLID OR STRANDED
 LR7189 Certified	MILITARY P/N AND CLASS
22-16 AWG SOLID OR STRANDED	NOT APPLICABLE

STAMP 105 AMP 22-18* APPROX AS SHOWN
22-16 TERMINALS ARE STAMPED 22-18 IN
ACCORDANCE WITH MILITARY SPECIFICATION
MIL-T-7928, COMMERCIAL WIRE RANGE IS 22-16
105 INDICATES STUD SIZE



5000	ON TAPE	53832-2
----	LOOSE PIECE	53832-1
QUANTITY	PACKAGING TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: NOT APPLICABLE
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	WIRE CROSS SECTIONAL AREA RANGE: 0.26-1.65mm ² [509-3,260] CIR MILS SOLID OR STRANDED
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR ENGINEERING AND CONSTRUCTION AND THE CONTROLLING ENGINEERING OR CONSTRUCTION DEPARTMENT SHOULD BE CONTACTED FOR THE LATEST REVISION.

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES	2 PLG DEC # - 3 PLG DEC # - ANGLES # -	MATERIAL PHOSPHOR BRONZE PER ASTM B-103 ANNEALED	FINISH TIN PLATE	0.00254L 0.00100J MIN THK PER MIL-T-10727
---	--	---	---------------------	--

DR 3-29-93 TA BRIKMAN	 AMP Incorporated Harrisburg, PA 17105-3608	NAME TERMINAL, SHORT SPRING SPADE, SOLISTRAND™	
CHK 3-29-93 DA PATTERSON			
APPD 3-29-93 DE MILLER			
APPD 3-29-93 JL MECKLEY			
PRODUCT SPEC -			
APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO
-	C	00779	C-53832
WEIGHT -	SCALE 10.1	SHEET	1 OF 1

TERMINAL, SHORT
SPRING SPADE, SOLISTRAND™

10 SEP 1993 12.59.05 AMP36463 21E139A>DEPT1133>DL13133>11 COI 1CTDAND-11 INI TWT

CUSTOMER DRAWING