

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

76160-5010

Status:

Active

Overview:

Impact™ Backplane Connector and Cable Assembly System

Description:

Impact™ 100 Ohm 4 Pair Right Angle Daughtercard Receptacle, Right Guided, 10 Columns, 120 Circuits, Plated Through Hole Dimension 0.46mm, Lead-Free

Documents:

3D Model

Drawing (PDF)

Product Specification PS-76060-999 (PDF)

Application Specification AS-76060-990 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E29179

General

Product Family

Series

Application

Application Tooling Documents

Component Type

Electrical Model

Overview

Product Name

Style

UPC

Backplane Connectors

76160

Conventional, Coplanar, Daughtercard

TM-622018799

PCB Receptacle

Yes

Impact™ Backplane Connector and Cable Assembly System

Impact™

N/A

800756929156

Physical

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Durability (mating cycles max)

First Mate / Last Break

Flammability

Guide to Mating Part

Keying to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Number of Columns

Number of Pairs

Number of Rows

Orientation

PC Tail Length

PCB Locator

PCB Retention

PCB Thickness - Recommended

Packaging Type

Pitch - Mating Interface

Pitch - Termination Interface

Plating min - Mating

Polarized to PCB

Temperature Range - Operating

Termination Interface: Style

120

120

Black

200

No

94V-0

Yes

None

High Performance Alloy (HPA)

Gold

Tin

High Temperature Thermoplastic

15.548/g

10

4

12

Right Angle

1.20mm

No

None

1.00mm

Tray

1.90mm

1.90mm

0.762µm

Yes

-55°C to +85°C

Through Hole - Compliant Pin



image - Reference only

Series

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

76160Series

Mates With

76155 Impact™ 100 Ohm Vertical Header, 76500 Impact™ 100 Ohm Right Angle Male Header

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Impact Daughter	0622024300
Card Extraction Tool	
Daughter Card	0622018641
Module Installation	
Press-In Tool	

Electrical

Current - Maximum per Contact	0.75A
Data Rate	25.0 Gbps
Impedance	100#
Shield Type	N/A
Shielded	No
Voltage - Maximum	30V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Application Specification	AS-76060-990
Electrical Model Document	EE-76160-003
Product Specification	PS-76060-999
Sales Drawing	SD-76160-004

This document was generated on 12/11/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[76160-5010](#)