

DVD-S58 DVD Player

FIND ANOTHER MODEL

Model number: DVD-S58

★★★★★ 2 Reviews

Print this | Share this



Product no longer available for purchase.

- **1080p upconversion with HDMI output:**
Convert DVD content to 1080p resolution
- **VIERA Link™:** Control multiple compatible devices with one remote
- **Multi-format DVD/CD/MP3 playback:** Plays back content stored in several different DVD formats

Online Order Assistance

- [Track your order](#)
- [Print your invoice](#)
- [Read our shipping FAQs](#)
- [Register your product](#)

Accessories

- [Find accessories for your product](#)

Contact Us

- [Live Chat](#)
- [Phone](#)
- [Email](#)
- [Mail](#)
- [International Support](#)

Operating Manuals

FAQs

Tech Specifications

Warranty & Care Plans

Accessories

Drivers & Downloads

FORMAT:

+R/+R (DL)/ +RW Playback Capability	Video
DVD	DVD Video
DVD-R/DVD-RW/DVD-R DL	DVD Video MP3 (DVD-R / DVD-R DL only) JPEG (DVD-R / DVD-R DL only)
CD	CD-DA Video CD SVCD
CD-R/-RW	CD-DA Video CD SVCD MP3 JPEG
Television Signal System	NTSC

VIDEO:

Video D/A Converter	108MHz/12-bit
Progressive Scanning	Yes
Zoom	Yes
Picture Mode Selection	Yes (Brightness , Contrast, Hue, Saturation, Sharpness)
Black Level Control	Yes
Up-Conversion to 1080p Playback	Yes (1080p/1080i/720p/576p/480p)

AUDIO:

Digital Output (Dolby Digital® / DTS™)	Yes
Audio D/A Converter	192kHz/24-bit

INPUT/OUTPUT:

HDMI Output	Yes
Component Video Out (Y, PB, PR)	Yes
Video Out	Yes
2ch Audio Out	Yes
Digital Audio Out	Coaxial (1)

CONVENIENCE:

Audio/JPEG Navigation Menu	Yes
Energy Star® Compliant	Yes
HDMI-CEC	Yes

SPECIFICATIONS:

Horizontal Resolution	More than 500 lines
Video S/N	More than 53dB
Audio S/N	90dB
Power Source	AC 120V, 60Hz
Power Consumption	10W
Dynamic Range	80dB
Dimensions (H x W x D)	1-1/2 x 16-15/16 x 8-7/32
Weight (lb.) [Approx.]	3.4

