





▲ **HARDWARE SUPPLIED**
ON SWITCH


NOTES:

1. ALL DIMENSION IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REF. ONLY
4. CONTACT RATING SWITCHING: 150mA, 250V AC/DC
350mA, 110V AC/DC
5. CONTACT RATING (NON-SWITCHING) 5A
6. CONTACT MATERIAL: SILVER over COPPER ALLOY.
7. OPERATING FORCE: 425±100 CM/STANDARD
8. OPERATING TEMP: -30° to 85°C
9. CIRCUIT SP: 5 POSITIONS, 30° INDEX.
10. DIELECTRIC STRENGTH 1000V RMS min. @ SEA LEVEL
11. ▲ DENOTES CRITICAL PARAMETER.
12. HARDWARE SUPPLIED ON SWITCH- SEE BELOW STOPRING, LOCKWASHER, & HEXNUT



CONTACT CONFIGURATION
TIMING: SHORTING (MBB)

TERMINATION DETAIL
SCALE 2X



TITLE			
KC15A9.501SLS			
E-SWITCH®			
A	13306	RELEASED FOR PRODUCTION	7/21/03
REV.	ECN No.	DESCRIPTION	DATE
			CHKD
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED			
SCALE	1.5:1	DATE	7/21/03
DR	AR	DWG	G527543
REV	A		