

**Part Number: 79108-0057**

2.00mm Pitch Milli-Grid™ Flex-to-Board Vertical Receptacle Dual Row Through-Hole, 0.76µm Gold (Au) Selective Plating, 16 Circuits, Tin/Lead

Image not available

Status:	OBSOLETE
Replacement:	791081057
Series:	79108
Category:	FFC/FPC Connectors
Overview:	Milli-Grid™ Connector System

Series image - Reference only

Product Environmental Compliance

EU RoHS: Not RoHS Compliant
China RoHS: 
REACH SVHC:
Low-Halogen Status: Not Reviewed

Part Detail**General**

Status	Obsolete
Category	FFC/FPC Connectors
Series	79108
Obsolete Date	2005/06/01
Overview	Milli-Grid™ Connector System
Product Name	Milli-Grid™

Physical

Circuits (Loaded)	16
Contact Position	Top
Durability (mating cycles max)	50
Entry Angle	90° Angle
Number of Rows	2
Orientation	Right Angle
PC Tail Length	1.27mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	0.60mm
Packaging Type	Tube
Pitch - Mating Interface	2.00mm
Polarized to PCB	No
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-55°C to +105°C
Termination Interface: Style	Through Hole
Wire/Cable Type	FFC/FPC

Electrical

(Please review the Product Specification for specific details.)

Current - Maximum per Contact	1A
Voltage - Maximum	125V

Solder Process Data

Replacement RoHS Compliant Part Number	0791081057
--	------------

Material Info**Application Tooling**

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application**Tooling**

[Check our list of old tooling that used to be available for this part](#)

