

PC Board Frame (continued)

| No. of Positions | Dimensions (mm) |      | Housing Material | Housing Color | Keying                 | Part Number       |
|------------------|-----------------|------|------------------|---------------|------------------------|-------------------|
|                  | A               | B    |                  |               |                        | Tab Header        |
| 3                | 5.0             | 10.1 | PA 6.6 GF, V-0   | black         | –                      | <b>1-964575-3</b> |
| 4                | 7.5             | 12.6 | PA 6.6 GF, V-0   | black         | –                      | <b>1-964575-4</b> |
|                  |                 |      |                  | black         | b                      | 2-964575-4        |
|                  |                 |      |                  | black         | c                      | 3-964575-4        |
|                  |                 |      |                  | black         | d                      | 4-964575-4        |
|                  |                 |      |                  | black         | –                      | <b>1-964575-5</b> |
| 5                | 10.0            | 15.1 | PA 6.6 GF, V-0   | black         | d                      | 2-964575-5        |
|                  |                 |      |                  | black         | b, e                   | 3-964575-5        |
|                  |                 |      |                  | black         | –                      | <b>1-964575-6</b> |
| 6                | 12.5            | 17.6 | PA 6.6 GF, V-0   | black         | d, f                   | 2-964575-6        |
|                  |                 |      |                  | black         | d, e                   | 3-964575-6        |
|                  |                 |      |                  | black         | –                      | <b>1-964575-7</b> |
| 7                | 15.0            | 20.1 | PA 6.6 GF, V-0   | black         | d                      | 2-964575-7        |
|                  |                 |      |                  | black         | b, e, g                | 3-964575-7        |
|                  |                 |      |                  | natural       | b, e, g                | 4-964575-7        |
|                  |                 |      |                  | black         | –                      | <b>1-964575-8</b> |
| 8                | 17.5            | 22.6 | PA 6.6 GF, V-0   | black         | b, c, d, h             | 2-964575-8        |
|                  |                 |      |                  | black         | –                      | <b>1-964575-9</b> |
|                  |                 |      |                  | black         | c, d, i                | 2-964575-9        |
| 9                | 20.0            | 25.1 | PA 6.6 GF, V-0   | black         | –                      | <b>1-964575-0</b> |
|                  |                 |      |                  | black         | a, b, c, e, h, i, k    | 3-964575-0        |
| 10               | 22.5            | 27.6 | PA 6.6 GF, V-0   | black         | –                      | <b>1-964576-1</b> |
|                  |                 |      |                  | black         | b, c, e, g             | 2-964576-1        |
|                  |                 |      |                  | black         | –                      | <b>1-964576-2</b> |
| 11               | 25.0            | 30.1 | PA 6.6 GF, V-0   | black         | k                      | 2-964576-2        |
|                  |                 |      |                  | natural       | k                      | 3-964576-2        |
|                  |                 |      |                  | black         | f, g, h, i, j, k, l    | 4-964576-2        |
|                  |                 |      |                  | natural       | c, d, e, i, j, k, l    | 5-964576-2        |
|                  |                 |      |                  | natural       | –                      | 6-964576-2        |
|                  |                 |      |                  | black         | –                      | <b>1-964576-3</b> |
| 12               | 30.0            | 32.6 | PA 6.6 GF, V-0   | black         | –                      | <b>1-964576-3</b> |
| 13               | 30.0            | 32.6 | PA 6.6 GF, V-0   | black         | –                      | <b>1-964576-3</b> |
| 15               | 35.0            | 40.1 | PA 6.6 GF, V-0   | black         | a, d, g, i, j, n, o, p | <b>2-964576-5</b> |
| 17               | 30.0            | 45.1 | PA 6.6 GF, V-0   | black         | d, r                   | <b>2-964576-7</b> |

Preferred Types are printed bold.

Note: Additional keying variants available on request