

Technical drawing of a shaft with dimensions and tolerances:

- Top view:
 - Left end: $E \pm .015 (.38 \text{ mm})$
 - Inner diameter: $C \pm .015 (.38 \text{ mm})$
 - Right end: $B \pm .012 (.30 \text{ mm})$
- Bottom view:
 - Left end: $D \pm .015 (.38 \text{ mm})$
 - Length: F
 - Right end: $A \pm .008 (.20)$

SEE CURRENT PRICE SHEET FOR
PART NUMBER SUFFIX DESIGNATION
FOR PACKAGE SIZE.

- A ± .008 (.20 mm)

PANDUIT * PART NO.	DESCRIPTION	BUNDLE DIA.		A in. (mm)	B in. (mm)	C in. (mm)	D in. (mm)	E in. (mm)	F in. (mm)	MINIMUM LOOP TENSILE 2"/MIN. lbs. (N)	WEIGHT lbs/(kg) per 100/pcs
		MIN. in. (mm)	MAX. in. (mm)								
DT4EH	13.5 IN. LONG TIE	.020 (.51)	3.875 (98.4)	.059 (1.50)	.495 (12.57)	.490 (12.45)	.812 (20.62)	.718 (18.24)	13.5 ±.150 (343) (±3.81)	250 (1112)	2.6 (1.18)
DT8EH	27 IN. LONG TIE	.020 (.51)	8.0 (203.2)	.059 (1.50)	.495 (12.57)	.490 (12.45)	.812 (20.62)	.718 (18.24)	27.0 ±.150 (686) (±3.81)	250 (1112)	4.4 (2.0)
DT14EH	48 IN. LONG TIE	.020 (.51)	14.0 (355)	.059 (1.50)	.495 (12.57)	.490 (12.45)	.812 (20.62)	.718 (18.24)	48.0 ±1.50 (1219) (±38.1)	250 (1112)	7.5 (3.4)
DT15EH	53 IN. LONG TIE	.020 (.51)	15.0 (381)	.059 (1.50)	.495 (12.57)	.490 (12.45)	.812 (20.62)	.718 (18.24)	53.0 ±1.50 (1346) (±38.1)	250 (1112)	8.1 (3.7)
DT28EH	96 IN. LONG TIE	.020 (.51)	28.0 (711)	.059 (1.50)	.495 (12.57)	.490 (12.45)	.812 (20.62)	.718 (18.24)	96.0 ±1.50 (2438) (±38.1)	250 (1112)	13.8 (6.3)
DT44EH	144 IN. LONG TIE	.020 (.51)	44.0 (1117)	.059 (1.50)	.495 (12.57)	.490 (12.45)	.812 (20.62)	.718 (18.24)	144.0 ±1.50 (3658) (±38.1)	250 (1112)	20.6 (9.3)

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

PANDUIT CORP. TINLEY PARK, ILLINOIS

EXTRUDED CABLE TIES (EXTRA HEAVY)

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

MAT'L:
STRAP & HEAD -
BLACK ACETAL
EACH HEAD HAS TWO,
TYPE 302 STAINLESS
STEEL BARBS

DRAWING NO.
SS-27250
SHEET 1 OF 2

A
SIZE

---	---			CHANGED WIDTH TOLERANCE FROM ±.008 TO ±.012.	---	---				
4	11/10/08	ERW		CHANGED WIDTH (DIM 'B') ON ALL PARTS FROM .500 TO .495	SS-27250	4				
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP			