

受控 CONTROLLED DOCUMENT				
编号 P/N	40-97XXM	版本 Rev	02	日期 Rel'd Date
Jul11,11				



Description: 97 Series Solder Style Panel & Cable Mount D-Sub Connectors

Part No: 40-97xxM

Application: For Cable

Crimp Tool: N/A

Impedance: N/A

Fequency Range: 0-15 MHz


Material: Housing Steel Nickel plated
Insulator PBT+Fiber-glass UL94-V0 White
Contact Cu-alloy, Gold plated



RoHS Compliance: Yes

Technical Detail: N/A

P/N	Pins	A	B	C	D
40-9709M	9	30.80	24.99	16.92	19.20
40-9715M	15	39.15	33.32	25.25	27.70
40-9725M	25	53.00	47.04	38.96	41.10
40-9737M	37	69.30	63.50	55.42	57.30

DRAWING NO. 40-97XXM									
REVISIONS									
01	OFFICIAL RELEASE								
	02-20-09	T W	B Y	T					
02	CHANGE SHELL PLATING FROM YELLOW ZINC TO NICKEL; CHANGE DIMENSIONS: 3.50MAX TO 3.8REF; D DIMENSION FOR 40-9725M FROM 41.28 TO 41.10; ADD DIMENSIONS: 1.25MAX; 5.6MAX;								
	03-25-11	J J	J J	D					ECO-11-0055



A			TOLERANCE UNLESS OTHERWISE SPECIFIED		DRAWN BY JEAN.JIN		DATE 03-25-11		 cinch CONNECTIVITY SOLUTIONS a bel group				
			DECIMALS	mm	CHECKED BY JEAN.JIN		DATE 03-25-11						
			X	± 0.5	APPROVED BY DONALD		DATE 03-25-11		TITLE 97 SERIES SOLDER STYLE PANEL & CABLE MOUNT D-SUB CONNECTORS				
			X.X	± 0.3	U/M		mm						
			X.XX	± 0.1									
		ANGLES	± 0.5°				SHEET 1 OF 1			DRAWING NO. 40-97XXM-CUST		SIZE A	
THIS DRAWING WAS PRODUCED BY COMPUTER, DO NOT SCALE DRAWING OR UPDATE MANUALLY.													

SOLID EDGE RESSELLER.COM