

Search Results

Evaluate

- FAQ's

How to Buy

- Bill of Material

- Favorite Products List

- Locate Distributor

Home > Product On-Line Catalog > Search Results >

Current refinements (click ☐ to remove) Search Tips 

☒ Text Search: 'F612D5-5F248Y'

Your search criteria matched only one product, shown below

F612D5-5F248Y



- Pass all TIA/EIA-568-B.3 performance requirements
- FOCIS-5 compliant
- Insertion loss per mated pair: .50dB typical; .75dB max.
- Factory terminated, assembled and 100% tested for insertion loss
- Insertion loss data recorded for every multimode cable assembly
- Lifetime traceability of test data to a Q.C. number on each cable assembly
- 2-pin alignment assures consistent repeatable performance
- * MTP is a registered trademark of US Conec Ltd.

• Part Number	F612D5-5F248Y
• RoHS Compliancy Status	RoHS directive is not applicable
• Note	Intended for use in fixed installations which are outside the scope of RoHS
• Part Description	Female MTP* to female MTP* twelve strand fiber optic cable assembly (one female MTP* connector on each end on ribbon interconnect cable) 62.5/125µm. Outside diameter: 5mm x 2.5mm.
• Product Type	MTP* 12 Fiber Interconnect Cable Assemblies
• Length (ft.)	247
• Length (m)	75.6
• Fiber Compatibility	62.5/125µm
• Fiber Type	Multimode
• Cable Color	Orange
• Cable Type	Duplex
• CE Compliant	No
• Connector 1 Type	MTP* Connector
• Connector 2 Type	MTP* Connector
• End Configurations	MTP* to MTP*
• Fiber Count	12
• Flammability Rating	Plenum (OFNP)
• Pricing Description	248 ft – MTP*-MTP* Plenum Interconnect Cable Assembly 62.5µm
• Min. Order UOM	PC
• Min. Order Qty.	1
• BOM Qty. (# of Pkgs.)	0
• Add to Favorite Product List	☐

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.