

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0002081101](#)
Status: **Active**
Description: Claspcon™ Crimp Terminal Socket, Tin (Sn) Plated Brass Contact, 16-24 AWG, Reel


Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Crimp Terminals
Series	1881
Application	Power
Comments	Interleaf Paper on First Few Wraps Only
Crimp Quality Equipment	Yes
Product Name	Claspcon™
UPC	800753615922

Physical	
Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.326/g
Packaging Type	Reel
Plating min - Mating	0.508µm
Plating min - Termination	0.508µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	3.50mm max.
Wire Size AWG	16, 18, 20, 22, 24
Wire Size mm²	N/A

Material Info	
Old Part Number	1881-2C1A

Reference - Drawing Numbers	
Product Specification	RPS-1881-001, RPS-1881-002
Sales Drawing	SD-1881-*



Series image - Reference only

EU ELV Not Relevant	
EU RoHS Compliant REACH SVHC Contains SVHC(2015 June 15): No Halogen-Free Status Low-Halogen Need more information on product environmental compliance? Email productcompliance@molex.com Please visit the Contact Us section for any non-product compliance questions.	China RoHS China ROHS ELV
Green Image Not Relevant	

Search Parts in this Series
[1881](#) Series

Mates With
16-06-0005

Application Tooling FAQ <i>Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.</i> Global	
Description	Product #
Extraction Tool	0011030006
Mini-Mac™	0638924200
Applicator	
Terminator Die	0011402083

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION