


# Battery and Connector Probes

## 100671 PROBE



### PROBE SPECIFICATIONS

**Minimum Centers:** .175 (4.45)  
**Current Rating:** 3 amps continuous  
(Individual probe in free air @ ambient temperature)  
**Spring Force:** 5.1 oz. (145g) @ .027 (0.69) travel  
**Typical Resistance:** < 10 mΩ  
**Maximum Travel:** .040 (1.02)\*  
**Working Travel:** .027 (0.69)

### MATERIALS


**Barrel:** Nickel/silver, gold plated  
**Spring:** Stainless steel, gold plated  
**Plunger:** Beryllium copper, gold plated

\* not recommended for use at maximum travel

## HOW TO ORDER

100671-000

## 101111 PROBE



### PROBE SPECIFICATIONS

**Minimum Centers:** .029 (0.75)  
**Current Rating:** 6 amps continuous  
(Individual probe in free air @ ambient temperature)  
**Spring Force:** 1.5 oz. (43g) @ .022 (0.55) travel  
**Typical Resistance:** < 50 mΩ  
**Maximum Travel:** .025 (0.58)  
**Working Travel:** .022 (0.55)

### MATERIALS

**Barrel:** Phosphor bronze, gold plated  
**Spring:** Music wire, gold plated  
**Plunger:** Phosphor bronze, gold plated

## HOW TO ORDER

101111-008

Specifications subject to change without notice. Dimensions in inches (millimeters)