





- 1

INSERTS: GLASS-FILLED PBT OR GLASS-FILLED NYLON, UL94V-0 RATED. COLOR: BLACK
SHELLS: CARBON STEEL; RETAINER CLIP: STAINLESS STEEL.
- 2

SHELLS: 5.08µm [0.00200] MIN ZINC WITH YELLOW CHROMATE COATING.
CONTACTS: GOLD FLASH PLATED FOR LENGTH OF 2.54[0.100] MIN FROM MATING END, 2.54µm [0.00100] MIN TIN OR TIN-LEAD FOR A LENGTH OF DIMENSION A FROM OPPOSITE END, BOTH OVER 1.27µm [0.00050] MIN NICKEL.
- 3

SHELLS: 5.08µm [0.00200] MIN ZINC WITH YELLOW CHROMATE COATING.
CONTACTS: 0.76µm [0.00030] MIN GOLD FOR A LENGTH OF 2.54µm [0.00100] MIN FROM MATING END, 2.54µm [0.00100] MIN TIN OR TIN-LEAD FOR A LENGTH OF DIMENSION A FROM OPPOSITE END, BOTH OVER 1.27µm [0.00050] MIN NICKEL.
OR
GOLD FLASH OVER PALLADIUM-NICKEL 0.76µ [0.00030] MIN TOTAL, FOR LENGTH OF 2.54 [0.100] MIN FROM MATING END, 2.54µm [0.00100] MIN TIN OR TIN-LEAD FOR A LENGTH OF DIMENSION A FROM OPPOSITE END, BOTH OVER 1.27µm [0.00050] MIN NICKEL.



DETAIL D

	OBSOLETE	PER DETAIL D	3.18 [0.125]	3	205738-9
SUPSD BY 205738-7	-	4.78 [0.188]	2	205738-8	
	-	4.78 [0.188]	3	205738-7	
SUPSD BY 205738-3	-	16.54 [0.651]	2	205738-6	
SUPSD BY 205738-3	-	16.54 [0.651]	3	205738-5	
SUPSD BY 205738-3	-	10.85 [0.427]	2	205738-4	
	-	10.85 [0.427]	3	205738-3	
SUPSD BY 205738-1	-	3.18 [0.125]	2	205738-2	
	-	3.18 [0.125]	3	205738-1	
RETAINER CLIP		A	CONTACT FINISH	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. POLIGNONE 01FEB07	TE Connectivity	
DIMENSIONS: mm[INCHES]		CHK E. BRIANT 01FEB07	NAME RECEPTACLE ASSEMBLY, SIZE 3, 25 POSN, VERTICAL, AMPLIMITE HDP	
	0 PLC ± -	PRODUCT SPEC 108-40025	SIZE CAGE CODE DRAWING NO RESTRICTED TO	
	1 PLC ± -	APPLICATION SPEC 114-40013		
	2 PLC ± 0.13 [0.005]			
	3 PLC ± -			
	4 PLC ± -			
MATERIAL 1	FINISH 2 3	WEIGHT -	A1 00779 C-205738	
		CUSTOMER DRAWING		
		SCALE NTS	SHEET 1 OF 1	REV Y