

Search within category

GO

BUY NOW

DESIGN / INSTALL



HB0A1M2BN12E1

Horizontal power strip 30 A, 120V, 12 NEMA 5-20R receptacles, two 20 A single pole magnetic breaker/on-off switch with integral switch guard, and 10' power cord with NEMA L5-30P twist lock plug. UL and c-UL Listed. Dimensions: 1.7H x 17.0W x 6.5D (43mm x 431mm x 165mm)

This part number has been obsoleted with no replacement. [Click here](#) to contact customer service for further assistance.

Specs

Packaging Details

Documents

OM Obsolete Code	OBSOLETE
Rack PDU Type	Basic Rack PDU
Monitoring	NA
Remote Outlet Switching	No
Mount Orientation	Horizontal
Current Rating (Amps)	30A
Input Voltage	120V - Single Phase
Plug Type	NEMA L5-30P
Output Voltage	120V
Receptacle Type	NEMA 5-20R Duplex
Total Number of Outlets	12
Depth (In.)	6.50
Depth (mm)	165.1
Height (In.)	1.72
Height (mm)	43.7
Width (In.)	17.10
Width (mm)	434.3
Tool-Less Button Spacing (In.)	NA
Tool-Less Button Spacing (mm)	NA
No. of Rack Spaces	1
Surge Suppression	No
Amps	30A
Cable Length	3
Length (In.)	22.75
UL Recognized	Yes
Voltage	120V
RoHS Compliancy Status	Compliant
Min. Order Qty.	1