




AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN DK SCHRUM 02FEB96		AMP Incorporated Harrisburg, PA 17105-3608		
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	RECOMMENDED OPERATING TEMPERATURE: 170° MAX		DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±0.20 [.008] 3 PLC ±- 4 PLC ±- ANGLES ±-	CHK WJ VOCKROTH 02FEB96	NAME TERMINAL, CENTERLINE TONGUE, AMPOWER, WIRE SIZE: 350 MCM		
		VOLTAGE RATING: NOT APPLICABLE					APVD JL MECKLEY 02FEB96	SIZE A3	
	FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	WIRE CROSS SECTIONAL AREA RANGE: 0.16-0.19mm ² [325-375] MCM SOLID OR STRANDED	MATERIAL COPPER PER ASTM B-75 ANNEALED	FINISH TIN PLATE 0.00381 [.000150] MIN THK PER MIL-T-10727	PRODUCT SPEC 108-30200	APPLICATION SPEC -	CAGE CODE 00779	DRAWING NO C-277145
	FOR ORDER ENTRY	1-800-526-5142				WEIGHT .242 lbs		SCALE 1:1	SHEET 1 OF 1
CUSTOMER DRAWING									