

2,8 mm	1,2...C manuell	0,3m	CS-Mount	94°17'
4,0 mm	1,2...C manuell	0,2m	CS-Mount	63°53'
4,8 mm Fixfocus	1,8...C manuell	0,2m	C-Mount	55°07'
6 mm	1,2...C manuell	0,2m	C-Mount	43°33'
8 mm	1,2...C manuell	0,3m	CS-Mount	33°19'
8,5 mm	1,5...C manuell	0,2m	C-Mount	31°52'
12 mm	1,2...22 manuell	0,2m	C-Mount	22°04'
16 mm	1,4...22 manuell	0,3m	C-Mount	16°55'
25 mm	1,4...22 manuell	0,3m	C-Mount	10°58'
35 mm	1,6...16 manuell	0,35m	C-Mount	7°51'
50 mm	2,8...22 manuell	0,9m	C-Mount	5°30'
50 mm	1,4...C manuell	1,0m	C-Mount	5°30'
75 mm	1,4...C manuell	1,2m	C-Mount	3°40'

A0014

A0021

A0016

A0053

A0011

A0047

A0035

A0026

A0007

A0051

A0052

A0049

A0008



A0016
4,8mm



A0011
8mm



A0026
16mm



A0007
25mm