

 [Live Product Chat](#)



Always EU RoHS/ELV Compliant (Statement of Compliance)

- Barrier Strip
- Barrier Style = Single Row, Tri-Barrier
- Block Style = Open Bottom with Standoffs
- 8.26 mm Centerline
- Vertical Mount Angle

[View all Features](#) | [Find Similar Products](#)

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

NEW!

- [4PCV-XX-006 ASSEMBLY \(PDF, English\)](#)

- None Available

- None Available

- None Available

- None Available

- 2D Drawing (DXF, Version K1)
- 3D Model (IGES, Version K1)
- 3D Model (STEP, Version K1)

- Product Line Information

- Tooling

List all Documents

- Product Type = Barrier Strip
- Mount Angle = Vertical
- Number of Positions = 3
- CSA File No. = LR30811
- UL Recognized = File No. E54800
- Screw Material = Steel
- Mounting Ears = Without
- Comment = Do not order Screw and Captive Clamp in combination with other top hardware.; Other options available upon request, consult our Product Information Center.

- Screw Plating = Bright Zinc/Chrome
- Mounting Style = Direct (All Positions Filled)

- [Top Hardware](#) = Wire Clamp Combo Head
- Number of Levels = Single
- End Barriers = Without
- Bracket = Without
- Screw Head Type = Phil-Slot
- Current Rating, Max. (Amps.) = UL: 20A, CSA: 25A
- Mounting Insert = Without

- Barrier Style = Single Row, Tri-Barrier
- Block Style = Open Bottom with Standoffs
- Centerline (in [mm]) = 0.325 [8.26]
- Number of Rows = Single
- Terminal Style = Printed Circuit Pin 5.08 [.200]
- Wire Range (mm [AWG]) = 0.30-3.00² [22-12]

- Mounting Options = None

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

- Brand = Buchanan