

Isolierkörpermaterial
 PBT, UL94V-0

Kontaktmaterial
 Phosphorbronze

Kontaktfläche
 Ni, Sn

Kontaktwiderstand
 15mΩ max

Isolationswiderstand
 10000MΩ min

Strombelastbarkeit
 1A

Betriebstemperatur
 -40°C - +105°C

Betriebsspannung
 100V AC

Prüfspannung
 500V AC

Verpackung
 Stangenverpackung

Insulator material
 PBT, UL94V-0

Contact material
 Phosphor bronze

Plating
 Ni, Sn

Contact resistance
 15mΩ max

Insulation resistance
 10000MΩ min



Current rating
 1A

Operating temperature
 -40°C - +105°C


Operating voltage
 100V AC

Test voltage
 500V AC

Packing
 Tube packing



Dimensions			
No. of contacts	A	B	C
20	15.50	15.50	5.08
28	18.05	18.05	7.62
32	18.05	20.60	7.62
44	23.50	23.50	12.70
52	25.88	25.88	15.24
68	31.66	31.66	20.32
84	36.66	36.66	25.40



Bestellcode / Ordercode

Polzahl

20 / 28 / 32 / 44 / 52 / 68 / 84

No. of contacts

20 / 28 / 32 / 44 / 52 / 68 / 84

A - CCS 0 xx - Z - T

Bitte „x“ durch die geeignete Option ersetzen
 Please replace „x“ appropriate option

Cable
assemblies

D-Sub / Hoods
Centronics

Multiflex -
DIN41651

Modular

USB
IEEE1394

Switches

Powercords
Powerinlets

DIN41612
Hardmetric

MiniDIN

Sockets / Strips
Jumper

Terminal Blocks

Memory Card

FFC / FPC