

GDME LED 24 YE

Industrial Connectors:Rectangular connectors GDM-series:Type A EN 175301-803 (DIN 43650) / ISO 4400:Electronic inserts for GDME


Product description

Description	function indicator (LED) with freewheeling diode
Type	GDME LED 24 YE
Order No.	831 863-001
Standard	DIN EN 175 301-803-A
Construction type	A

Description of Wiring

LED color	LED yellow
-----------	------------

Drawing



Technical data

Rated voltage	UC 24 V
Rated current	8 A

Environmental conditions

Temperature range	-40 °C to +110 °C
-------------------	-------------------

Packaging unit

Packaging unit	50 pieces
----------------	-----------