

**IP55**

SUITABILITY

**CPB Series Compact Pendant Stations, Two Button, NEMA 4X**

| Description                                                              | Catalog Number |
|--------------------------------------------------------------------------|----------------|
| Single-speed normally open-normally closed without mechanical interlock. | <b>CPB20</b>   |
| Single-speed with mechanical interlock between pushbuttons.              | <b>CPB21</b>   |
| Two-speed with mechanical interlock between pushbuttons.                 | <b>CPB22</b>   |

Note: Included with product: nylon cord grip and sealing washer (must be installed to achieve NEMA 4X rating).


Indication label pack. Cord dia. range .375–.625 in. (9.5–15.9)

Ambient temperatures: 25°F to 140°F (32°C to 60°C).

Typical applications: Package electric motor hoists. Remote control of machinery.

**Contact Ratings, CPB Series**

| Single-Speed | Voltage | Current |
|--------------|---------|---------|
| AC           | 120V    | 6A      |
| 35% PF       | 240V    | 3A      |
| DC           | 125V    | 1.1A    |
| IND          | 250V    | .55A    |
| Two-Speed    | Voltage | Current |
| AC           | 120V    | 3A      |
| 35% PF       | 240V    | 1.5A    |

**CPB21****Wiring Diagram CPB2 Series**

\*Mechanical "floating ball" interlock prevents activating both Pushbuttons simultaneously.

**PBS Series Heavy Duty Pendant Pushbutton Stations, NEMA 3R**

| Description             | Catalog Number |
|-------------------------|----------------|
| 2 button, single speed. | <b>PBS2</b>    |
| 2 button, two speed.    | <b>PBS22</b>   |
| 4 button, single speed. | <b>PBS4</b>    |
| 4 button, two speed.    | <b>PBS42</b>   |
| 6 button, single speed. | <b>PBS6</b>    |
| 6 button, two speed.    | <b>PBS62</b>   |
| 8 button, single speed. | <b>PBS8</b>    |
| 8 button, two speed.    | <b>PBS82</b>   |


**Product Dimensions, PBS Series**

| Style    | A              | Approx. Wt. Assembled | Catalog Number |
|----------|----------------|-----------------------|----------------|
| 2 button | 7.88" (200.0)  | 2.5 lbs               | <b>PBS2</b>    |
| 4 button | 13.69" (347.6) | 4.5 lbs               | <b>PBS4</b>    |
| 6 button | 18.0" (457.2)  | 5.5 lbs               | <b>PBS6</b>    |
| 8 button | 22.31" (566.7) | 7.5 lbs               | <b>PBS8</b>    |

Note: Housing: Yellow vinyl rubber.

**Contact Interrupting Ratings, PBS Series**

| Two-Speed Single Break    | Voltage | Current |
|---------------------------|---------|---------|
| AC                        | 120V    | 6A      |
| 35% PF                    | 240V    | 3A      |
| DC                        | 125V    | .4A     |
| IND                       | 250V    | .2A     |
| Single-Speed Double Break | Voltage | Current |
| AC                        | 120V    | 6A      |
| 35% PF                    | 240V    | 3A      |
| DC                        | 125V    | 1.1A    |
| IND                       | 250V    | .55A    |



Dimensions in Inches (mm)