

FEATURES AND OPTIONS

- 15 pins in a 9 position shell
- 26 pins in a 15 position shell
- 44 pins in a 25 position shell
- 62 pins in a 37 position shell
- Hardware options include: threaded inserts, hex stand-offs, board locks and grounding straps
- Gold plated contacts
- Tin plated shell

SPECIFICATIONS

MATERIALS

Shell: Tin plated steel

Insulator: PBT thermo plastic, black color, 30% glass filled self-extinguishing, UL94V-0 rated

Contact material: Pin: Brass

Socket: Phosphor Bronze

Contact plating: Gold over nickel

ELECTRICAL

Current rating: 5.0 Amps




Dielectric strength: 1000Vac min.

Insulation resistance: 5000M ohm min.


Operating temperature range: -55°C~ to +125°C

HOW TO ORDER

AHDFXXA-KG-TXXX-R (RoHS Compliant)



26. 44. 62 POSITIONS



15 POSITIONS

DIMENSIONS

# of pins	A	B	C	E	F
15	16.33	24.99	30.81	7.04	2.29
	0.643	0.984	1.213	0.277	0.090
26	24.66	33.32	39.14	6.88	2.29
	0.971	1.312	1.541	0.271	0.090
44	38.38	47.04	53.04	6.88	2.29
	1.511	1.852	2.088	0.271	0.090
62	54.84	63.50	69.32	6.99	2.41
	2.159	2.500	2.729	0.275	0.095