


Pin Header Right Angled 2,54 mm

Series

088



Rated current	3,0 A
Rated voltage	250 VRMS / VDC
	Please consider air- and creepage distances
Withstand voltage	500 VRMS for one minute
Material contact	Copper alloy
Material insulator	High temp. thermoplast UL94V-0
Operating temperature	-40°C to +105°C
Max. processing temper.	260°C for 10 seconds

All dimensions in mm.

pitch
2,54

termination


contact
size

□ 0,64



max.
pincount
050/100/120Product
group
3

Variation



PCB Layout




1



2



3



see figure left

see figure left

see figure left

see figure left

available in variation

A

B

C

W

7,40

3,50

3,30

3,90

1

2

3

8,70

4,80

3,30

3,90

1

2

3

10,00

6,10

3,30

3,90

1

2

3

10,80

6,90

3,30

3,90

1

2

3

13,80

9,90

3,30

3,90

1

2

3

15,90

12,00

3,30

3,90

1

2

3

17,70

13,80

3,30

3,90

1

2

3

18,90

15,00

3,30

3,90

1

2

3

21,00

17,10

3,30

3,90

1

2

3

Plating:

T = Sn

F = Au

S = Selective Au

* No. of contacts:

Variation 1 = 001 - 050

Variation 2 = 002 - 100

Variation 3 = 003 - 120

Variation (1,2,3)

No. of contacts *
(001 - 120)

Plating contact (T,F,S)

A (1/100 mm)
e.g. 1000 = 10,00 mm

www.mpe-connector.de

CS17081_V2

Order code:

088 - 2 - 2222 - 0 - 2 - XS0 - 2222

Mating series	094	095	096	097	298	299	099	100	098	366	111	115	612	613	114	122	120	430		
see page	4-22	4-23	4-24	4-25	4-26	4-27	4-28	4-29	4-30	4-31	4-32	4-33	4-34	4-35	4-37	4-38	4-39	6-10		