






Rating	400mA 32VAC 125mA 125VAC 100mA 50VDC	Mounting Hole	Circuit Diagram
Contact Resistance	50m ohm Max		
Insulation Resistance	DC 500V 100M ohm Min.		
Dielectric Strength	AC 1000V 1minute		
Operation Temperature	-25°C~85°C		
Function	2P SPST OFF-(ON)	Thickness:1.5~4.0mm	

() = Momentary Function



MATERIAL:

Frame: Black, Nylon 66(94-v2)

Actuator: Red, Nylon 66(94-v2)

Base: Black, PBT(94-V0)

Terminals: Gold plated, Copper

Waterproof: IP67

RoHS Compliant

CW INDUSTRIES
Southampton, Pa. 18966
Tel 215.355.7080/www.cwind.com

Date Drawn: 12/01/09

Rev. 0

Unit: mm

Checked By: **GG**

Title:
PUSH BUTTON SWITCH

CW P/N:
GPB556A05BR