

**TENMA®**


ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION,  
WHETHER IN WHOLE OR IN PART, CAN BE REPRODUCED  
WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC  
TECHNOLOGY.

SPC-F005.DWG

## REVISIONS

DOC. NO. SPC-F005 \* Effective: 7/8/02 \* DCP No: 1398

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1355	A	Released	JWM	12/1/03	HO	12/19/03	JC	1/21/04

**Specifications:**

- Rating: 1,200V AC/DC, 12 amps
- Internal Resistance: 15 milliohms
- Operating Temp: -20°C to 80°C

Materials:

- Cable Type: Flexible PVC, Conductor: 0.75mm<sup>2</sup>
- Body: Polyamide (Nylon)
- Plug: Bronze and Brass, Nickel Plated

DISCLAIMER:  
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED  
HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE  
BELIEVE TO BE ACCURATE AND RELIABLE. SINCE  
CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE  
USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT  
FOR THE INTENDED USE AND ASSUME ALL RISK AND  
LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:  
UNLESS OTHERWISE  
SPECIFIED,  
DIMENSIONS ARE  
FOR REFERENCE  
PURPOSES ONLY.

DRAWN BY: Jeff McVicker DATE: 12/1/03  
CHECKED BY: Hisham Odish DATE: 12/19/03  
APPROVED BY: John Cole DATE: 1/21/04

DRAWING TITLE:  
**Retractable Sleeve 4mm Plug to Plug Lead, Red**  
SIZE DWG. NO. A 76-093 ELECTRONIC FILE 84N2135.dwg REV A  
SCALE: NTS U.O.M.: Inches SHEET: 1 OF 1