



DATA CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO TROMPETER ELECTRONICS INC. AND SHALL NOT BE DISCLOSED, COPIED OR USED FOR PROCUREMENT OR MANUFACTURE WITHOUT EXPRESS WRITTEN PERMISSION.

INCH	MM
.005	0.13
.026	0.66
.030	0.76
.088	2.24
.093	2.36
.461	11.71
.470	11.94
.717	18.21
1.022	25.96



REVISIONS			3000-0065 SH 1		
REV	EO	DESCRIPTION	DWN	APPROVED	DATE
A	7391	L/M PART NOS 1/2/3 WERE 8000-1838/8000-1488-1/8000-1523	CKH	F3, BHM, AT	1-30-87



5. SUBMINATURE
TWINAX/TRIAX PUSH ON
SOLDER POT PANEL JACK

4 SOLDER POT ACCEPTS .026
MAX DIA CONDUCTOR

3. MAX PNL THK .088

2. FINISH: TFS-1A (NICKEL)

1. ALL DIM ARE IN INCHES

QTY	DESCRIPTION		PART NUMBER		ITEM
TOL UNLESS SPECIFIED .XX ± .XXX ±.005 .XXXX ± ANGLES ±		TROMPETER ELECTRONICS, INC.	PL151		
DWN	JEH	5-26-81	MATERIAL	CODE IDENT	DRAWING NO.
CHK	TW	5-27-81	—	14949	3000-0065
ENGR					REV
APPR	AT	7-2-81	SCALE 4/1	DATE 7-7-81	A
NEXT ASSY			SHEET 1 OF 2		