



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION ,19 .
© COPYRIGHT 19 BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST	P	F	REVISIONS			DATE	APPD
				ZONE	LTR	DESCRIPTION		
G	86				E	REV PER 063A-0561-01	08OCT02	JR



1 CIRCULAR MIL RANGE: 275-325 MCM
2 TIN PL 0.00381 [0.000150] MIN THK PER MIL-T-10727



325821		
PART NO		
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± 0.51 [0.020] 3 PLC DEC ± - ANGLES ± - MATERIAL ANNEALED COPPER ASTM B-75 FINISH		
DR 02/28/90 DK SCHRUM CHK 23JAN95 MS FEHER APPD 23JAN95 WJ VOCKROTH APPD 23JAN95 TL SHUTTER PRODUCT SPEC 108-30200 APPLICATION SPEC - WEIGHT .369 LB		
AMP INCORPORATED Harrisburg, Pa. 17105 NAME TERMINAL, AMPPOWER™ WIRE SIZE: 300 MCM SIZE C CAGE CODE 00779 DRAWING NO 325821 SCALE 1:1 SHEET 1 OF 1		