



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION . 19 .
© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.


REVISIONS					DATE	APPROVED
REV	ZONE	LTR	DESCRIPTION			
1		A	REV. & REL. AF-0568 / PAR		11-2-84	RLT / GY
2		B	OBS PER AF-2304		4-13-88	TAG / BY
3		C	REACTIVATE -1 AF-6801		7/17/90	DKS /




- 1. DIMENSIONS IN BRACKETS ARE IN INCHES.
- 2. CONTINUOUS STRIP ON REELS WITH TERMINALS ON 32.51 [1.28] CENTERS.



SECT. A-A



SECT. B-B



1.80-3.20 [0.071-0.126]		0.3-0.9mm ² [#22-18]		63361-1	
INSULATION RANGE		WIRE RANGE		PART NO	
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ±0.25 [0.010] ANGLES ±		CONTRACT NO		AMP AMP INCORPORATED Harrisburg, Pa.	
		4-25-84			
		CHK G Yotter 4/30/84		NAME	
		MATERIAL		APPD D Schwach 4/30/84	
BRASS 0.46 THK [0.018]		DSGN APPD			
FINISH		OTHER APPD			
NONE				SIZE B	
				FSCM NO 00779	
				DRAWING NO 63361	
				SCALE —H—	
				SHEET	

METRIC