




- 1 STAMP "AMP 12-10*", LOCATION APPROX AS SHOWN.
- 2 TONGUE THICKNESS IS 1.00±0.05
- 3 APPLIES TO EDGE OF METAL WIRE BARREL TO CENTER OF STUD HOLE.
- 4 WIRE INSULATION DIA RANGE 3.8-6.4
- 5 BODY - COPPER PER ASTM B152
SLEEVE - COPPER PER ASTM B152
INSULATION - NYLON
- 6 BODY - TIN PLATE PER ASTM B545
SLEEVE - TIN PLATE PER ASTM B545
INSULATION - COLOR-YELLOW
- 7 105°C MAX OPERATING TEMP.
- 8 300 VOLT MAX
- 9 2.62-6.64mm² [5,180-13,100 CMA]
SOLID OR STRANDED

2500	ON TAPE & REEL	2-165028-1
500	LOOSE PIECE	165028
QTY	PACKAGE TYPE	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN jr ruth 29MAR07	TE Connectivity			
		CHK T MICHIELUTTI 29MAR07				
		APVD T MICHIELUTTI 29MAR07	NAME			
		PRODUCT SPEC	TERMINAL RING TONGUE, PIDG, WIRE SIZE 12-10			
		APPLICATION SPEC	-			
		WEIGHT	-			
		CUSTOMER DRAWING	SIZE A3	CAGE CODE 00779	DRAWING NO C-165028	RESTRICTED TO -
			SCALE 4:1	SHEET 1 of 1	REV A4	