

# G81-1800



Models may vary from the image shown

## Just 19" - quality is not a question of size!

Compact design - that's our 19 inch PC keyboard. Its unique FTSC membrane contact system guarantees a long service life and reliability.

## Key benefits

- Mechanical individual keys with membrane contact switches (FTSC technology)
- High quality and compact 19" PC keyboard - space-saving and ergonomic
- Codeset 3 support (PS/2 connection only) e.g. for Unix computers
- Robust and reliable
- High-quality keyboard for professional use
- Can also be delivered without "Windows® keys" (101/102 keys)

## Technical Data:

### Layout (country or language):

Product dependant, see table "Models"

### Housing colour:

Product dependant, see table "Models"

### Key colour:

Product dependant, see table "Models"

### Weight (product):

approx. 1300 g

### Total weight (with packaging):

approx. 1600 g

### Cable Length:

approx. 1.75 m

### Storage Temperature:

-20°C to 60°C

### Operating Temperature:

0°C to 50°C

### Current Consumption:

typ. 16 mA

### Interface:

Product dependant, see table "Models"

### Product approvals:

- cURus 
- VDE GS 
- c-tick 
- CE 
- FCC 

### System requirements:

Product dependant, see table "Models"

### Delivery Volume:

- G81-1800
- Printed instructions

### Dimensions (product):

approx. 405 x 180 x 44 mm

### Packaging dimensions:

approx. 460 x 270 x 50 mm

### Reliability:

- MTBF > 80,000 hours
- MCBF > 10 bill. operations

### Keyboard:

- Key technology: FTSC
- Service life, standard key: > 50 million key operations
- Operation characteristics: Linear
- Inscription technology: Laser
- Inscription layout: Standard
- Number of Keys: Product dependant, see table "Models"

### Packaging Unit:

- Number of products in the master package: 54
- Number of master packages per pallet: 2

### Warranty:

2 years

Errors, technical changes and delivery possibilities excepted.  
Technical information refers only to the specifications of the products. Features may differ from the information provided.

## Models:

(possible country/layout versions, others available on request)

	Product name	Order number	EAN code	Layout (country or language)	Housing colour	Key colour	Interface	System requirements	Number of Keys
1	G81-1800	G81-1800LADE-0	4025112046742	Germany	light grey	light grey	DIN	DIN Interface	102
2	G81-1800	G81-1800LAAES-0	4025112015298	Spain	light grey	light grey	DIN	DIN Interface	102
3	G81-1800	G81-1800LAAFR-0	4025112046759	France	light grey	light grey	DIN	DIN Interface	102
4	G81-1800	G81-1800LAAGB-0	4025112046735	UK	light grey	light grey	DIN	DIN Interface	102
5	G81-1800	G81-1800LAAUS-0	4025112011931	US English	light grey	light grey	DIN	DIN Interface	101
6	G81-1800	G81-1800LAMDE-0	4025112039980	Germany	light grey	light grey	DIN	DIN Interface	105
7	G81-1800	G81-1800LAMES-0	4025112008900	Spain	light grey	light grey	DIN	DIN Interface	105
8	G81-1800	G81-1800LAMEU-0	4025112040450	US English with EURO symbol	light grey	light grey	DIN	DIN Interface	104
9	G81-1800	G81-1800LAMIT-0	4025112023958	Italy	light grey	light grey	DIN	DIN Interface	105
10	G81-1800	G81-1800LAMSL-0	4025112046766	Slovenia	light grey	light grey	DIN	DIN Interface	105
11	G81-1800	G81-1800LPADE-0	4025112046773	Germany	light grey	light grey	PS/2	PS/2 connection	102
12	G81-1800	G81-1800LPAFR-0	4025112046780	France	light grey	light grey	PS/2	PS/2 connection	102
13	G81-1800	G81-1800LPAGB-0	4025112046797	UK	light grey	light grey	PS/2	PS/2 connection	102
14	G81-1800	G81-1800LPAUS-0	4025112011948	US English	light grey	light grey	PS/2	PS/2 connection	101
15	G81-1800	G81-1800LPMBB-0	4025112045653	Bulgaria	light grey	light grey	PS/2	PS/2 connection	104
16	G81-1800	G81-1800LPMBE-0	4025112010408	Belgium	light grey	light grey	PS/2	PS/2 connection	105
17	G81-1800	G81-1800LPMBE-2	4025112044519	Belgium	black	black	PS/2	PS/2 connection	105
18	G81-1800	G81-1800LPMCH-0	4025112036521	Switzerland	light grey	light grey	PS/2	PS/2 connection	105
19	G81-1800	G81-1800LPMCH-2	4025112044526	Switzerland	black	black	PS/2	PS/2 connection	105
20	G81-1800	G81-1800LPMDE-0	4025112004759	Germany	light grey	light grey	PS/2	PS/2 connection	105
21	G81-1800	G81-1800LPMDE-2	4025112044533	Germany	black	black	PS/2	PS/2 connection	105
22	G81-1800	G81-1800LPMDK-0	4025112046803	Denmark	light grey	light grey	PS/2	PS/2 connection	105
23	G81-1800	G81-1800LPMDK-2	4025112044540	Denmark	black	black	PS/2	PS/2 connection	105
24	G81-1800	G81-1800LPMES-0	4025112017544	Spain	light grey	light grey	PS/2	PS/2 connection	105
25	G81-1800	G81-1800LPMES-2	4025112044557	Spain	black	black	PS/2	PS/2 connection	105
26	G81-1800	G81-1800LPMEU-0	4025112040832	US English with EURO symbol	light grey	light grey	PS/2	PS/2 connection	104
27	G81-1800	G81-1800LPMEU-2	4025112044618	US English with EURO symbol	black	black	PS/2	PS/2 connection	104

	Product name	Order number	EAN code	Layout (country or language)	Housing colour	Key colour	Interface	System requirements	Number of Keys
28	G81-1800	G81-1800LPMFR-0	4025112017537	France	light grey	light grey	PS/2	PS/2 connection	105
29	G81-1800	G81-1800LPMFR-2	4025112044564	France	black	black	PS/2	PS/2 connection	105
30	G81-1800	G81-1800LPMGB-0	4025112011979	UK	light grey	light grey	PS/2	PS/2 connection	105
31	G81-1800	G81-1800LPMGB-2	4025112044571	UK	black	black	PS/2	PS/2 connection	105
32	G81-1800	G81-1800LPMGR-2	4025112050374	Greece	black	black	PS/2	PS/2 connection	105
33	G81-1800	G81-1800LPMHU-0	4025112055102	Hungary	light grey	light grey	PS/2	PS/2 connection	105
34	G81-1800	G81-1800LPMIT-0	4025112017520	Italy	light grey	light grey	PS/2	PS/2 connection	105
35	G81-1800	G81-1800LPMIT-2	4025112044588	Italy	black	black	PS/2	PS/2 connection	105
36	G81-1800	G81-1800LPMNL-0	4025112017551	Netherlands	light grey	light grey	PS/2	PS/2 connection	105
37	G81-1800	G81-1800LPMNO-0	4025112046810	Norway	light grey	light grey	PS/2	PS/2 connection	105
38	G81-1800	G81-1800LPMNO-2	4025112044595	Norway	black	black	PS/2	PS/2 connection	105
39	G81-1800	G81-1800LPMPL-0	4025112055096	Poland	light grey	light grey	PS/2	PS/2 connection	105
40	G81-1800	G81-1800LPMPO-0	4025112039812	Portugal	light grey	light grey	PS/2	PS/2 connection	105
41	G81-1800	G81-1800LPMRB-0	4025112010415	English (US) / Cyrillic	light grey	light grey	PS/2	PS/2 connection	104
42	G81-1800	G81-1800LPMSE-0	4025112017513	Sweden / Finland	light grey	light grey	PS/2	PS/2 connection	105
43	G81-1800	G81-1800LPMSE-2	4025112044601	Sweden / Finland	black	black	PS/2	PS/2 connection	105
44	G81-1800	G81-1800LPMST-0	4025112047367	Czech Republic	light grey	light grey	PS/2	PS/2 connection	105
45	G81-1800	G81-1800LUMCH-2	4025112052828	Switzerland	black	black	USB	USB connection	105
46	G81-1800	G81-1800LUMDE-0	4025112017346	Germany	light grey	light grey	USB	USB connection	105
47	G81-1800	G81-1800LUMDE-2	4025112056079	Germany	black	black	USB	USB connection	105
48	G81-1800	G81-1800LUMES-0	4025112019401	Spain	light grey	light grey	USB	USB connection	105
49	G81-1800	G81-1800LUMEU-2	4025112050640	US English with EURO symbol	black	black	USB	USB connection	104
50	G81-1800	G81-1800LUMFR-2	4025112056062	France	black	black	USB	USB connection	105
51	G81-1800	G81-1800LUMGB-0	4025112056048	UK	light grey	light grey	USB	USB connection	105
52	G81-1800	G81-1800LUMGB-2	4025112056055	UK	black	black	USB	USB connection	105
53	G81-1800	G81-1800LUMUS-0	4025112017353	US English	light grey	light grey	USB	USB connection	104
54	G81-1800	G81-1860LAMDE-0	4025112039980	Germany	light grey	light grey	DIN (AT/XT adjustable)	DIN Interface	105
55	G81-1800	G81-1860LAMES-0	4025112008900	Spain	light grey	light grey	DIN (AT/XT adjustable)	DIN Interface	105

	Product name	Order number	EAN code	Layout (country or language)	Housing colour	Key colour	Interface	System requirements	Number of Keys
56	G81-1800	G81-1860LAMUS-0	4025112008917	US English	light grey	light grey	DIN (AT/XT adjustable)	DIN Interface	104