


343-1850
 343-1861
 343-1873

1/1

Interface Module

Interface module for ribbon cable acc. to IEC 603-1 / DIN 41651

Data sheet



Description			Item-No.	Pack.-unit pcs
Interface module with male connector	No. of poles	Dimensions "L"		
	10	35 mm / 1.38 in	289-611	1
	14	40 mm / 1.57 in	289-612	1
	16	45 mm / 1.77 in	289-613	1
Interface module with male connector for female connector with IDC acc. to DIN 41651 part 1 and 2. Short and long latches for the female connector, with and without strain relief, are shipped loose.			Technical Data	
- Mounting carrier for DIN 35 rail with lateral marking system. - Marking with the WMB multi marking system or with marking strips with cover.			Operating voltage	AC/DC 125 V
			Nominal current	1 A
			Connector contact	Phosphor-bronze
				0.38 µm Au selectively over 1.3 µm Ni
			Performance level	3
			Nominal voltage	
			acc. to VDE 0110/1.89	125 V / 1.5 kV / 2
			Dimensions incl. mounting carrier (LxWxH)	(Lx85x46*) mm (Lx3.35x1.89*) in * from upper edge of DIN 35 rail
			Wire connection	CAGE CLAMP® terminal strips (WAGO series 736)
				0.08-2.5 mm² / AWG 28-12 ** ** AWG12: THHN, THWN
			Stripped length	5-8 mm / 0.22 in
			Mating direction	vertical
			Ambient operating temperature	-20 °C...+55 °C
			Storage temperature	-40 °C...+70 °C
			Standards / prescriptions	IEC 603-1 / DIN 41651 Part 1 and 2