



## APC Replacement Battery Cartridge #35

Part Number: RBC35



[Technical Specifications](#) [Product Overview](#) [Documentation](#) [Ratings and Reviews](#)

### Batteries & Runtime

|                                                                                  |
|----------------------------------------------------------------------------------|
| Battery Type                                                                     |
| Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof |
| Battery mounting                                                                 |
| Stand alone battery stack                                                        |
| Battery manufacturer                                                             |
| --                                                                               |
| Expected Battery Life (years)                                                    |
| 3 - 5                                                                            |
| RBC™ Quantity                                                                    |
| 1                                                                                |

### Physical

|                      |
|----------------------|
| Net Weight           |
| 3.08 lbs. (1.40 kg)  |
| Maximum Height       |
| 2.60 inches (66 mm)  |
| Maximum Width        |
| 2.28 inches (58 mm)  |
| Maximum Depth        |
| 5.28 inches (134 mm) |
| Shipping Weight      |
| 3.68 lbs. (1.68 kg)  |
| Shipping Width       |
| 5.76 inches (146 mm) |
| Shipping Height      |
| 3.70 inches (94 mm)  |
| Shipping Depth       |
| 7.38 inches (187 mm) |
| Color                |
| Black                |

### Environmental

|                              |
|------------------------------|
| Operating Environment        |
| 32 - 104 °F (0 - 40 °C)      |
| Operating Relative Humidity  |
| 0 - 95%                      |
| Operating Elevation          |
| 0-10000 feet (0-3000 meters) |
| Storage Temperature          |
| 5 - 113 °F (-15 - 45 °C)     |

|                                                    |
|----------------------------------------------------|
| Storage Relative Humidity<br>0 - 95%               |
| Storage Elevation<br>0-50000 feet (0-15000 meters) |
| <b>Conformance</b>                                 |
| Standard Warranty<br>1 year repair or replace      |
| <b>Sustainable Offer Status</b>                    |
| PEP<br>Available in Documentation tab              |
| EOL<br>Available in Documentation tab              |

\*Except where noted, all prices are Estimated Resale Price (ERP) - Without Tax/VAT. Pricing in other locations and sites may vary.